


T50R**111-04804**

T18S – T250XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For the routing, bundling and securing of cables, pipes and hoses.

Base Data**Application Method**

Quick, simple fixing by hand or with HellermannTyton tensioning tools

Colour

Red (RD)

Package Content

100

Quantity per

Bag

Recommended Application Tool

MK3SP, MK3PNSP2, MK7P, MK7, MK7HT, MK20, MK6, MK6PN, MK9, MK9HT, MK21

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

Product Dimensions**Bundle Diameter max (Imperial)**

1.97 "

Bundle Diameter max (Metric)

50

Bundle Diameter min (Imperial)

.06 "

Bundle Diameter min (Metric)

1.5

Length L (Imperial)

7.9 "

Length L (Metric)

200

Minimum Tensile Strength (imperial)

50

Minimum Tensile Strength (N)

225

Width W (Imperial)

.18 "

Width W (Metric)

4.6