

### Product Description

#### Reference Standard

BS 4808 Part 2 Class 2 & Def Stan 61-12 (Pt6) Type 2

Multi-construction 1

#### Cable Construction


Conductor Material	: Tinned Copper
Conductor Area CSA	: 0.75mm <sup>2</sup>
Construction	: T0.2 ±0.008 × 24
Standard Dia.(mm)	: 1.13
Jacket Material	: PVC
Jacket Thickness	: 0.45
Jacket Dia.(±0.1mm)	: 2 +0.15/-0.1
*Jacket Colour	: See table below

#### Electrical Characteristics

Max. Conductor DC Resistance at 20°C(Ω/km)	: <25.2
Min. Insulation DC Resistance at 20°C(MΩ×km)	: 200
Rated Temperature	: -25°C to +85°C
Rated Voltage (V)	: 1,000
Flame Performance	: UL 1581 VW-1 IEC 60332-1



### Diagram:



# Defence Standard/BS4808 0.75mm<sup>2</sup> (24/0.2mm) PVC Equipment Wire

**multicomp** PRO

## Part Number Table

Description	*Jacket Colour	Part Number
Wire, 24/0.2mm, 100m	Black	PP000026
Wire, 24/0.2mm, 100m	Brown	PP000027
Wire, 24/0.2mm, 100m	Red	PP000028
Wire, 24/0.2mm, 100m	Orange	PP000029
Wire, 24/0.2mm, 100m	Yellow	PP000030
Wire, 24/0.2mm, 100m	Green	PP000031
Wire, 24/0.2mm, 100m	Blue	PP000032
Wire, 24/0.2mm, 100m	Violet	PP000033
Wire, 24/0.2mm, 100m	Grey	PP000034
Wire, 24/0.2mm, 100m	White	PP000035
Wire, 24/0.2mm, 100m	Pink	PP000036
Wire, 24/0.2mm, 100m	Green/Yellow	PP000037
Wire, 24/0.2mm, 100m	Yellow/Green	PP000038
Wire, 24/0.2mm, 500m	Black	PP000039
Wire, 24/0.2mm, 500m	Red	PP000040
Wire, 24/0.2mm, 500m	Blue	PP000041
Wire, 24/0.2mm, 500m	Grey	PP000042
Wire, 24/0.2mm, 500m	White	PP000043
Wire, 24/0.2mm, 500m	Pink	PP000044

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

**multicomp** PRO