




Specifications

Material	: Low Density Polyethylene
Colour	: UV Black, Natural
Operating Temperature	: -76°F to 190°F / -60°C to 88°C
Abrasion Resistance (Taber)	: 20mg loss per M cycles
Water Absorption % (D-570)	: 0.03
Di-Electric Constant (D-150)	: 2.6
UL Compliance	: UL Recognized

Diagram



Dimensions

Part Number	O.D	I.D	Wall Thickness	Right Hand Pitch
	Inches (mm)	Inches (mm)	Inches (mm)	Inches (mm)
PP002248	0.125 (3.175)	0.061 (1.594)	0.032 (0.812)	0.187 (4.749)
PP002247				
PP002250	0.187 (4.762)	0.127 (3.225)	0.03 (0.762)	0.25 (6.35)
PP002249				
PP002252	0.25 (6.35)	0.16 (4.064)	0.045 (1.143)	0.375 (9.525)
PP002251				
PP002254	0.375 (9.525)	0.271 (6.833)	0.052 (1.320)	0.438 (11.125)
PP002253				
PP002256	0.5 (12.7)	0.376 (9.55)	0.062 (1.574)	0.563 (14.3)
PP002255				
PP002258	0.625 (15.875)	0.501 (12.725)	0.062 (1.574)	0.625 (15.875)
PP002257				
PP002260	0.75 (19.05)	0.62 (15.748)	0.065 (1.651)	0.75 (19.05)
PP002259				
PP002262	1 (25.4)	0.84 (21.336)	0.08 (2.032)	1 (25.4)
PP002261				

Part Number Table

Description	Length	Part Number
0.125" Spiral Wrap, Polyethylene, UV Black	100ft/30.48m	PP002248
0.125" Spiral Wrap, Polyethylene, Natural		PP002247
0.187" Spiral Wrap, Polyethylene, UV Black		PP002250
0.187" Spiral Wrap, Polyethylene, Natural		PP002249
0.25" Spiral Wrap, Polyethylene, UV Black		PP002252
0.25" Spiral Wrap, Polyethylene, Natural		PP002251
0.375" Spiral Wrap, Polyethylene, UV Black		PP002254
0.375" Spiral Wrap, Polyethylene, Natural		PP002253
0.5" Spiral Wrap, Polyethylene, UV Black		PP002256
0.5" Spiral Wrap, Polyethylene, Natural		PP002255
0.625" Spiral Wrap, Polyethylene, UV Black		PP002258
0.625" Spiral Wrap, Polyethylene, Natural		PP002257
0.75" Spiral Wrap, Polyethylene, UV Black		PP002260
0.75" Spiral Wrap, Polyethylene, Natural		PP002259
1" Spiral Wrap, Polyethylene, UV Black		PP002262
1" Spiral Wrap, Polyethylene, Natural		PP002261

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.