


T18R

111-01816



T18S – T250XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For the routing, bundling and securing of cables, pipes and hoses.

#### Base Data

##### Application Method

Quick, simple fixing by hand or with HellermannTyton tensioning tools

##### Colour

Blue (BU)

##### Package Content

100

##### Quantity (Sold Unit / EDP)

100

##### Quantity per

Bag

##### Recommended Application Tool

MK20, MK3PNSP2, MK7P, MK7, MK3SP

#### Logistic and Packaging

##### Carton Quantity

0

##### EAN code

4031026104140

##### Quantity of Europallet

0

##### Weight (kg) (Metric)

0.28 kg

#### Material and Specifications

##### Flammability

UL94 V2

##### Material

Polyamide 6.6 (PA66)

##### Material Shortcut

PA66

##### Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

#### Product Dimensions

##### Bundle Diameter max (Imperial)

.86 "

##### Bundle Diameter max (Metric)

22 mm

##### Bundle Diameter min (Imperial)

.06 "

##### Bundle Diameter min (Metric)

1.5 mm

##### Length L (Imperial)

4 "

##### Length L (Metric)

100 mm

**Minimum Tensile Strength (imperial)**

18

**Minimum Tensile Strength (N)**

80 N

**Width W (Imperial)**

.10 "

**Width W (Metric)**

2.5

© HellermannTyton 2006