

Round LED

Warm White, 3mm

multicomp^{PRO}

RoHS
Compliant



Specifications:

Dice material	: InGaN
Emitted colour	: White
Lens colour	: Water clear
Dominant wavelength	: Y = 0.32
Viewing angle	: 36°
Luminous intensity (IV)	: 3,700mcd

Absolute Maximum Ratings (T_A = 25°C)

Reverse Voltage	5V
Reverse Current	10µA (V _R = 5V)
Electrostatics Discharge (ESD)	200V
Operating Temperature Range	-40°C to +85°C
Storage Temperature Range	-40°C to +100°C
Lead Soldering Temperature Range 1.6mm (1/16 inch) from body	260°C for 5 Seconds



Electrical/Optical Characteristics at T_A = 25°C

Parameter	Symbol	Minimum	Typical	Maximum	Unit	Test
Luminous Intensity	IV	2,500	3,700	5,500	mcd	IF = 20mA
Viewing Angle	2θ 1/2	-	36	-	degrees	
Peak Emission Wavelength	X	-	0.3	-	nm	-
Dominant Wavelength	Y	-	0.32	-		-
Spectral Line Half-Width	Δλ	-	-	-		-
Forward Voltage	VF	2.7	3.4	4	V	IF = 20mA
Power Dissipation	Pd	-	-	85	-	-
Peak Forward Current (Duty 1/10 at 1KHz)	IF (Peak)	-	-	100	-	-
Recommended Operating Current	IF (Rec)	-	20	-	mA	-



Round LED

Warm White, 3mm

White Typical Electrical Optical Characteristics Curves ($T_A = 25^\circ\text{C}$ Ambient Temperature Unless Otherwise Noted)



White Typical Electrical Optical Characteristics Curves ($T_A = 25^\circ\text{C}$ Ambient Temperature Unless Otherwise Noted)





Round LED


Warm White, 3mm

multicomp PRO

White Typical Electrical Optical Characteristics Curves (T_A = 25°C Ambient Temperature Unless Otherwise Noted)



Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
LED, 3mm, 36°, Warm White	MCL034SWC-YH1

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO