



Revision Number: 001.1

Issue date: 06/20/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE 3D 3840 WH 1L	IDH number:	2236049
Product type:	Acrylic Adhesive	Item number:	2236049
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: +1 (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Avoid breathing vapors, mist, or spray. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response:	IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
Storage:	Not prescribed
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

7 % of the mixture consists of ingredient(s) of unknown acute toxicity.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
(5-ethyl-1,3-dioxan-5-yl)methyl acrylate	66492-51-1	40 - 50
(Octahydro-4,7-methano-1H-indenediy)bis(methylene) diacrylate	42594-17-2	20 - 30
Polyurethane methacrylate resin	Proprietary	1 - 5
Trimethylolpropane triacrylate	15625-89-5	1 - 5
Isobornyl methacrylate	7534-94-3	1 - 5

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. Get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers.
Hazardous combustion products:	Oxides of carbon. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

- Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Refer to Section 8.
- Storage:** Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
(5-ethyl-1,3-dioxan-5-yl)methyl acrylate	None	None	None	None
(Octahydro-4,7-methano-1H-indenediyl)bis(methylene) diacrylate	None	None	None	None
Polyurethane methacrylate resin	None	None	None	None
Trimethylolpropane triacrylate	None	None	1 mg/m ³ TWA (SKIN)	None
Isobornyl methacrylate	None	None	None	None

- Engineering controls:** Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
- Respiratory protection:** Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
- Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
- Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

- Physical state:** Liquid
- Color:** Opaque, white
- Odor:** Mild
- Odor threshold:** Not available.
- pH:** Not available.
- Vapor pressure:** Not available.
- Boiling point/range:** > 150 °C (> 302°F)
- Melting point/ range:** Not available.
- Vapor density:** Not available.
- Flash point:** > 93.3 °C (> 199.94 °F)
- Flammable/Explosive limits - lower:** Not available.
- Flammable/Explosive limits - upper:** Not available.
- Autoignition temperature:** Not available.
- Flammability:** Not applicable
- Evaporation rate:** Not available.
- Solubility in water:** Not available.
- Partition coefficient (n-octanol/water):** Not available.
- VOC content:** < 3 %
- Viscosity:** 150 mPa.s
- Decomposition temperature:** Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Irritating organic vapours.
Incompatible materials:	Strong reducing agents. Free radical initiators. Inert gases. Oxygen scavengers. Strong oxidizing agents. Amines, strong alkalies Reactive metals.
Reactivity:	Not available.
Conditions to avoid:	Extremes of temperature and direct sunlight. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials. UV light.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation:	Inhalation of vapors or mists of the product may be irritating to the respiratory system.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Causes serious eye irritation.
Ingestion:	May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
(5-ethyl-1,3-dioxan-5-yl)methyl acrylate	None	Irritant, Allergen
(Octahydro-4,7-methano-1H-indenediyl)bis(methylene) diacrylate	None	No Records
Polyurethane methacrylate resin	None	No Records
Trimethylolpropane triacrylate	None	Irritant, Allergen
Isobornyl methacrylate	None	Irritant, Allergen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
(5-ethyl-1,3-dioxan-5-yl)methyl acrylate	No	No	No
(Octahydro-4,7-methano-1H-indenediyl)bis(methylene) diacrylate	No	No	No
Polyurethane methacrylate resin	No	No	No
Trimethylolpropane triacrylate	No	No	No
Isobornyl methacrylate	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.
Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Environmentally hazardous substance, liquid, n.o.s. ((5-Ethyl-1,3-dioxan-5-yl)methyl acrylate, (Octahydro-4,7-methano-1H-indenediyl)bis(methylene) diacrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. ((5-Ethyl-1,3-dioxan-5-yl)methyl acrylate, (Octahydro-4,7-methano-1H-indenediyl)bis(methylene) diacrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
Marine pollutant: (5-Ethyl-1,3-dioxan-5-yl)methyl acrylate, (Octahydro-4,7-methano-1H-indenediyl)bis(methylene) diacrylate

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis
CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA Section 313: None above reporting de minimis.
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Catherine Bimler, Regulatory Affairs Specialist

Issue date: 06/20/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.