Product datasheet Characteristics

CAD32E7

TeSys D control relay - 3 NO + 2 NC - <= 690 V -48 V AC standard coil





Main

Range	TeSys	
Product name	TeSys CAD	
Product or component type	Control relay	
Device short name	CAD	
Contactor application	Control circuit	

Complementary

22 NC 32 NC A2		
15 NO 44 NO 04 NO		
Main		
Range	TeSys	
Product name	TeSys CAD	
Product or component type	Control relay	
Device short name	CAD	
Contactor application	Control circuit	
Complementary		
Utilisation category	DC-13	
oundation datagory	AC-15	
	AC-14	
Pole contact composition	3 NO + 2 NC	
[Ue] rated operational voltage	<= 690 V AC 25400 Hz	
Control circuit type	AC at 50/60 Hz	
[Uc] control circuit voltage	48 V AC 50/60 Hz	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947	
[lth] conventional free air thermal current	10 A (at 60 °C)	
Irms rated making capacity	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1	
[lcw] rated short-time withstand current	100 A - 1 s	
	120 A - 500 ms 140 A - 100 ms	
Associated fuse rating	10 A gG conforming to IEC 60947-5-1	
[Ui] rated insulation voltage	600 V UL certified	
	600 V CSA certified	
Mounting ourset	690 V conforming to IEC 60947-5-1	
Mounting support	Rail Plate	
Connections - terminals	Screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Screw clamp terminals 2 cable(s) 14 mm²flexible without cable end	
Apr. C. 2020		



	Screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Screw clamp terminals 1 cable(s) 14 mm²solid without cable end
	Screw clamp terminals 2 cable(s) 14 mm²solid without cable end
Tightening torque	1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
Control circuit voltage limits	Operational: 0.81.1 Uc at 50 Hz Operational: 0.851.1 Uc at 60 Hz Drop-out: 0.30.6 Uc
Operating time	1222 ms coil energisation and NO closing 412 ms coil de-energisation and NO opening 419 ms coil energisation and NC opening 617 ms coil de-energisation and NC closing
Mechanical durability	30 Mcycles
Maximum operating rate	180 cyc/mn
Inrush power in VA	70 VA 50 Hz (at 20 °C)
Hold-in power consumption in VA	8 VA 50 Hz (at 20 °C)
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non-overlap time	1.5 ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact
Insulation resistance	> 10 MOhm
Mechanical robustness	Shocks control relay open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks control relay closed: 15 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations control relay open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations control relay closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6
Height	77 mm
Width	45 mm
Depth	84 mm
Net weight	0.58 kg

Environment

ZIIVII OIIIII OIII	
Standards	BS 4794
	EN 60947-5
	IEC 60947-5-1
	NF C 63-140
	VDE 0660
Product certifications	UL
	CSA
IP degree of protection	IP2x front face conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-4070 °C
Ambient air temperature for storage	-6080 °C
Operating altitude	3000 m without

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty 18 months