Product datasheet Characteristics

LC1D32N7

TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 32 A - 415 V AC coil





Main

Widin		
Range	TeSys	
Product name	TeSys D	
Product or component type	Contactor	
Device short name	LC1D	
Contactor application	Resistive load Motor control	
Utilisation category	AC-4 AC-1 AC-3	
Poles description	3P	
Power pole contact composition	3 NO	
[Ue] rated operational voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] rated operational current	32 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 50 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
Motor power kW	7.5 kW at 220230 V AC 50/60 Hz (AC-3) 15 kW at 380400 V AC 50/60 Hz (AC-3) 15 kW at 415440 V AC 50/60 Hz (AC-3) 18.5 kW at 500 V AC 50/60 Hz (AC-3) 18.5 kW at 660690 V AC 50/60 Hz (AC-3) 7.5 kW at 400 V AC 50/60 Hz (AC-4)	
Motor power HP (UL / CSA)	2 hp at 115 V AC 50/60 Hz for 1 phase motors 5 hp at 230/240 V AC 50/60 Hz for 1 phase motors 7.5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 10 hp at 230/240 V AC 50/60 Hz for 3 phases motors 20 hp at 460/480 V AC 50/60 Hz for 3 phases motors 30 hp at 575/600 V AC 50/60 Hz for 3 phases motors	
Control circuit type	AC at 50/60 Hz	
[Uc] control circuit voltage	415 V AC 50/60 Hz	
Auxiliary contact composition	1 NO + 1 NC	
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947	

Overvoltage category	III	
[lth] conventional free air thermal current	10 A (at 60 °C) for signalling circuit 50 A (at 60 °C) for power circuit	
Irms rated making capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947	
Rated breaking capacity	550 A at 440 V for power circuit conforming to IEC 60947	
[Icw] rated short-time withstand current	260 A 40 °C - 10 s for power circuit 430 A 40 °C - 1 s for power circuit 60 A 40 °C - 10 min for power circuit 138 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit	
Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 63 A gG at <= 690 V coordination type 2 for power circuit	
Average impedance	2 mOhm - Ith 50 A 50 Hz for power circuit	
[Ui] rated insulation voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified	
Electrical durability	1.65 Mcycles 32 A AC-3 at Ue <= 440 V 1.4 Mcycles 50 A AC-1 at Ue <= 440 V	
Power dissipation per pole	2 W AC-3 5 W AC-1	
Safety cover	With	
Mounting support	Plate Rail	
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508	
Product certifications	UL RINA CSA GOST DNV CCC LROS (Lloyds register of shipping) GL BV	
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1.510 mm²solid without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²solid without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²solid without cable end	
Tightening torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2	
Operating time	1222 ms closing 419 ms opening	
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical durability	15 Mcycles	

Maximum operating rate	3600 cvc/h 60 °C	
, ,	•	

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.30.6 Uc AC 50/60 Hz (at 60 °C) Operational: 0.81.1 Uc AC 50 Hz (at 60 °C) Operational: 0.851.1 Uc AC 60 Hz (at 60 °C)
Inrush power in VA	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	23 W at 50/60 Hz
Auxiliary contacts type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling circuit frequency	25400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non-overlap time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MOhm for signalling circuit

Environment

LITTION		
IP degree of protection	IP20 front face conforming to IEC 60529	
Protective treatment	TH conforming to IEC 60068-2-30	
Pollution degree	3	
Ambient air temperature for operation	-560 °C	
Ambient air temperature for storage	-6080 °C	
Permissible ambient air temperature around the device	-4070 °C at Uc	
Operating altitude	3000 m without	
Fire resistance	850 °C conforming to IEC 60695-2-1	
Flame retardance	V1 conforming to UL 94	
Mechanical robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms	
Height	85 mm	
Width	45 mm	
Depth	92 mm	
Net weight	0.375 kg	

Offer Sustainability

Green Premium product
REACh Declaration
Yes
Compliant EU RoHS Declaration
Yes
Yes
Yes
China RoHS declaration
Product Environmental Profile
End of Life Information
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Warranty

18 months