

## T50SSL5

## 126-02203



The arrowhead design, in conjunction with the supporting legs or disc, ensure a firm and secure fixing. The disc or legs take up any variation in panel thickness enabling one part to suit many applications. Both the RT and FBS versions are releasable and reusable and the FBS type have the added feature of a ladder type strap as opposed to the conventional serrated strap - this ladder type strap has the benefit of being very flexible.

With a diverse range of fixing possibilities (from 4.4mm to 8.0mm hole diameters and 0.5mm to 8.0mm panel thickness) this range of fixing ties is ideal for use in many different industries, including automotive, aerospace and panel building.

**Base Data****Colour**

Natural (NA)

**Package Content**

500

**Quantity per**

Bag

**Recommended Application Tool**

MK20, MK3PNSP2, MK3SP, MK7P, MK7

**Material and Specifications****Flammability**

UL94 V2

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Operating Temperature (Metric)**

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

**ROHS Conformity**

TRUE

**Product Dimensions****Bundle Diameter max (Metric)**

27

**Bundle Diameter min (Metric)**

1.5

**Height H (Metric)**

10

**Hole**

6.1-6.5

**Length L (Metric)**

135

**Minimum Tensile Strength (N)**

225

**Panel Thickness max.**

2.7

**Panel Thickness min.**

0.8

**Width W (Metric)**

4.6

