

352212KJT ✓ ACTIVE

CGS | CGS 3522

TE Internal #: 5-2176230-1

CGS 3522, Surface Mount Resistors, Power Resistor, 2 Terminations, Size Code 2512, Taped & Reeled, 5%, Thick Film, Resistance Range 1kΩ – 1MΩ Ω

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**

Number of Terminations: 2

Size Code: 2512

Packaging Method: **Taped & Reeled**

Tolerance: 5%

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Size Code	2512
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Tolerance	5%
Resistance Range	1kΩ – 1MΩ Ω
Resistance	12K Ω
Power Rating	3 W

Termination Features

Number of Terminations	2
Termination Type	Solder

Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

Dimensions

Dimensions	6.35 x 3.2 x .55 mm
------------	---------------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Model / Part # 2-2176230-7
3522 120R 5% 3W



TE Model / Part # 2176231-5
3522 15R 1% 3W



TE Model / Part # 2176230-2
3522 1R0 5% 3W




TE Model / Part # 4-2176230-2
3522 2K2 5% 3W



TE Model / Part # 2176230-1
3522 0R0 5% 3W

Also in the Series | CGS 3522



Surface Mount Resistors(220)

Customers Also Bought



TE Model / Part #1986775-6
SCREWLESS, SW,6P,5.08 PCB, Low Amp



TE Model / Part #3-88189-2
006 HOUSING FFC PIN DR 100CL



TE Model / Part #7-2176231-6
3522 13K 1% 3W



TE Model / Part #5-2176230-2
3522 15K 5% 3W




TE Model / Part #9-2176231-1
3522 56K 1% 3W



TE Model / Part #5-2301994-7
RJ45 JACK INT.MAG. 1GB 1X1



TE Model / Part #1-1461373-4
OMIH-SH-124L,394



TE Model / Part #1-1623782-9
SQM5 3K3 5% (METAL FILM)



Documents

Product Drawings

[3522 12K 5% 3W](#)

English

Datasheets & Catalog Pages

[SMD POWER RESISTORS - TYPE 3522 SERIES](#)

English