

Inductors for power circuits **Multilayer ferrite MLD** series (for automotive)











MLD2016 type













FEATURES

- O Being achieving high reliability by material application that was suitable for Automotive application and products design.
- O In complete monolithic structure with multilayer cluster, be reducing flux leakage
- Operating temperature range: -40 to +125°C (including self-temperature rise)
- Ocompliant with AEC-Q200

APPLICATION

- O ADAS, car multimedia (telematics), various ECUs, various modules
- O Application guides: Car Infotainment

PART NUMBER CONSTRUCTION

MLD	2016	S	1R0	М	Т	D25
Series name	L x W dimensions 2.0×1.6 mm	Characteristic type	Inductance (µH)	Height (mm max.)	Packaging style	Internal code

CHARACTERISTICS SPECIFICATION TABLE

Thickness	L		Measuring frequency	DC resistance	Rated current*	Part No.
Т					Itemp	
(mm)max.	(µH)	Tolerance	(MHz)	(Ω)	(mA)max.	
1.0	1.0	±20%	2	0.12±30%	1100	MLD2016S1R0MTD25
1.0	1.5	±20%	2	0.15±30%	1000	MLD2016S1R5MTD25
1.0	2.2	±20%	2	0.17±30%	900	MLD2016S2R2MTD25
1.0	3.3	±20%	2	0.23±30%	800	MLD2016S3R3MTD25
1.0	4.7	±20%	2	0.25±30%	750	MLD2016S4R7MTD25


^{*}Rated current(Itemp): current assumed when temperature has risen to 40°C max.

Measurement equipment

Measurement item	Product No.	Manufacturer	
L	4294A	Keysight Technologies	
DC resistance	Digital Milliohm Meter		
Rated current Isat	4285A+42841A+42842C	Keysight Technologies	

^{*} Equivalent measurement equipment may be used.

O Rated current vs. temperature characteristics (derating)






^{*}Please refer to the graph of rated current vs. temperature characteristics (derating) about the rating current at 85°C or more in temperature of the product.



MLD2016 type

L FREQUENCY CHARACTERISTICS




Measurement equipment

Product No.	Manufacturer	
4294A	Keysight Technologies	

^{*} Equivalent measurement equipment may be used.

■INDUCTANCE VS. DC BIAS CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer
4285A+42841A+42842C	Keysight Technologies

^{*} Equivalent measurement equipment may be used.



MLD2016 type


SHAPE & DIMENSIONS



Dimensions in mm


■PACKAGING STYLE

REEL DIMENSIONS




Dimensions in mm

■ RECOMMENDED LAND PATTERN




☐TAPE DIMENSIONS



Dimensions in mm

Туре	Α	В	K
MLD2016	2.25±0.10	1.85±0.10	1.10±0.10

■ RECOMMENDED REFLOW PROFILE



160min.	Taping	200min.	1
]
Drawing dir	ection		300min.

Dimensions in mm

□PACKAGE QUANTITY

Package quantity	3,000 pcs/reel

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range**	Individual weight
-40 to +125 °C	-40 to +125°C	12 ma

^{*} Operating temperature range includes self-temperature rise.

^{**} The storage temperature range is for after the assembly.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)

set forth in the each catalog, please contact us.

- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions