


Cat6a Keystone Jack Cable Assembly - Shielded, PoE+, RJ45 M/F, 18 in., Blue

MODEL NUMBER: N237A-F18N-WHSH



Simplifies the installation of PoE or PoE+ devices in above-ceiling applications where wall plates are impractical or unwanted.

Features

Specifically Designed for Use in Surveillance and Other PoE Applications

This Cat6a keystone jack assembly is recommended for above-ceiling applications where the use of wall plates is impractical or otherwise not ideal. The 18-inch cable connects your Cat6 premise wiring to an IP camera, wireless access point (WAP), LED lighting scheme, sound equipment or other PoE+ device installed high on a wall, ceiling or any other location far from a convenient power outlet.

Supports Power over Ethernet to Simplify Installation and Cut Down on Expenses

Because the N237A-F18N-WHSH supplies up to 24W of power to the connected PoE or PoE+ device, it saves you the expense and effort of purchasing, connecting and installing new electrical wiring, outlets and individual power supplies.

CMR-LP (0.5A) Certified for Cable Installations with Increased Power Levels

UL's Limited Power (LP) certification indicates the N237A-F18N-WHSH has been evaluated to handle the marked current under installation scenarios without exceeding the temperature rating of the cable. This CMR-LP-certified cable provides a simple way to prepare installations for increased power levels without having to worry about susceptible issues caused by excessive heat.

Highlights

- Cat6a STP patch cord rated for high-speed 10 Gbps communications
- Supports Power over Ethernet (PoE) and PoE+ up to 24 watts
- Ideal for security cameras, WAPs, LEDs and other ceiling-mount PoE+ devices
- Certified PoE+ cable saves you expense and effort of powering PoE devices individually
- Carries CMR-LP5 certification for withstanding temperatures up to 167°F (75°C)

Applications

- Connect a surveillance camera, WAP or other PoE+ device mounted high on a wall or ceiling
- Deliver power to PoE devices mounted in areas that are difficult to reach or have no electrical outlets

Package Includes

- N237A-F18N-WHSH Cat6a Keystone Jack Cable Assembly, RJ45 M/F, 18 in., Blue

Specifications

OVERVIEW	
UPC Code	037332250544
INPUT	
Cable Length (ft.)	1.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	0.457
Cable Length (in.)	18
Cable Length (cm)	45.7
PHYSICAL	
Cable Jacket Rating	CMR; CMR-LP
Cable Jacket Type	CMR; PVC
Cable Outer Diameter (OD)	7.3 +/- 0.3mm
Cable Shielding	F/UTP
Color	Blue
ENVIRONMENTAL	
Operating Temperature Range	14 ~ 140F (-10 ~ 60C)
Storage Temperature Range	-4 ~ 158F (-20 ~ 70C)
Relative Humidity	0% ~ 90% RH, Non-Condensing
COMMUNICATIONS	
Network Speed	10Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (FEMALE)
PoE Capability	15.4W (802.3af)
PoE Power Budget (Watts)	24
Contact Plating	Gold
PoE Type	Type 1 PoE (15.4W, IEEE 802.3af); Type 2 PoE+ (30W, IEEE 802.3at)
FEATURES & SPECIFICATIONS	
Technology	Cat6a
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>