



## Optocoupler, Phototransistor Output, Quad Channel, SOP-16, Half Pitch Mini-Flat Package



i179076-4



### FEATURES

- SOP (small outline package)
- Isolation test voltage, 3750 V<sub>RMS</sub> (1.0 s)
- High collector emitter voltage, V<sub>CEO</sub> = 70 V
- Low saturation voltage
- Fast switching times
- Temperature stable
- Low coupling capacitance
- End stackable, 0.050" (1.27 mm) spacing
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



### DESCRIPTION

The SFH6916 has a GaAs infrared emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a 16 pin 50 mil lead pitch miniflat package. It features a high current transfer ratio, low coupling capacitance, and high isolation voltage.

The coupling devices are designed for signal transmission between two electrically separated circuits.

### AGENCY APPROVALS

- UL1577, file no. E52744 system code U
- CSA 22.2 bulletin 5A, double protection
- DIN EN 60747-5-5 (VDE 0884)
- CQC GB4943.1-2011 (suitable for installation altitude below 2000 m)

| ORDERING INFORMATION   |                  |
|--|------------------|
| <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="border: 1px solid black; padding: 2px 5px;">S</div> <div style="border: 1px solid black; padding: 2px 5px;">F</div> <div style="border: 1px solid black; padding: 2px 5px;">H</div> <div style="border: 1px solid black; padding: 2px 5px;">6</div> <div style="border: 1px solid black; padding: 2px 5px;">9</div> <div style="border: 1px solid black; padding: 2px 5px;">1</div> <div style="border: 1px solid black; padding: 2px 5px;">6</div> </div> <p style="text-align: center;">PART NUMBER</p> |                  |
| <b>AGENCY CERTIFIED/PACKAGE</b>  | <b>CTR (%)</b>   |
| <b>UL, cUL</b>   | <b>50 to 300</b> |
| SOP-16, quad channel   | SFH6916          |

| ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified) |                         |                   |       |      |
|---|-------------------------|-------------------|-------|------|
| PARAMETER   | TEST CONDITION          | SYMBOL            | VALUE | UNIT |
| <b>INPUT</b>  |                         |                   |       |      |
| Reverse voltage   |                         | V <sub>R</sub>    | 6     | V    |
| DC forward current  |                         | I <sub>F</sub>    | 50    | mA   |
| Surge forward current   | t <sub>p</sub> ≤ 10 μs  | I <sub>FSM</sub>  | 2.5   | A    |
| Total power dissipation   |                         | P <sub>diss</sub> | 80    | mW   |
| <b>OUTPUT</b>   |                         |                   |       |      |
| Collector emitter voltage   |                         | V <sub>CE</sub>   | 70    | V    |
| Emitter collector voltage   |                         | V <sub>EC</sub>   | 7     | V    |
| Collector current   |                         | I <sub>C</sub>    | 50    | mA   |
|   | t <sub>p</sub> = 1.0 ms | I <sub>C</sub>    | 100   | mA   |
| Total power dissipation per channel   |                         | P <sub>diss</sub> | 150   | mW   |



| ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |  |           |                |                    |
|---|--|-----------|----------------|--------------------|
| PARAMETER   | TEST CONDITION   | SYMBOL    | VALUE          | UNIT               |
| <b>COUPLER</b>  |  |           |                |                    |
| Isolation test voltage between emitter and detector   | $t = 1.0\text{ s}$   | $V_{ISO}$ | 3750           | $V_{RMS}$          |
| Isolation resistance  | $V_{IO} = 500\text{ V}, T_{amb} = 25\text{ }^{\circ}\text{C}$          | $R_{IO}$  | $\geq 10^{12}$ | $\Omega$           |
|   | $V_{IO} = 500\text{ V}, T_{amb} = 100\text{ }^{\circ}\text{C}$         | $R_{IO}$  | $\geq 10^{11}$ | $\Omega$           |
| Storage temperature range   |  | $T_{stg}$ | - 55 to + 125  | $^{\circ}\text{C}$ |
| Ambient temperature range   |  | $T_{amb}$ | - 55 to + 100  | $^{\circ}\text{C}$ |
| Junction temperature  |  | $T_j$     | 100            | $^{\circ}\text{C}$ |
| Soldering temperature <sup>(1)</sup>  | max. 10 s dip soldering distance to seating plane $\geq 1.5\text{ mm}$ |           | 260            | $^{\circ}\text{C}$ |
| Total power dissipation   |  | $P_{tot}$ | 700            | mW                 |

**Notes**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.
- <sup>(1)</sup> Refer to reflow profile for soldering conditions for surface mounted devices.


| ELECTRICAL CHARACTERISTICS ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |   |             |      |      |      |               |
|---|---|-------------|------|------|------|---------------|
| PARAMETER   | TEST CONDITION                          | SYMBOL      | MIN. | TYP. | MAX. | UNIT          |
| <b>INPUT</b>  |   |             |      |      |      |               |
| Forward voltage   | $I_F = 5\text{ mA}$                     | $V_F$       |      | 1.15 | 1.4  | V             |
| Reverse current   | $V_R = 6\text{ V}$                      | $I_R$       |      | 0.01 | 10   | $\mu\text{A}$ |
| Capacitance   | $C_O$                                   | $C_O$       |      | 14   |      | pF            |
| Thermal resistance  |   | $R_{thja}$  |      | 1000 |      | K/W           |
| <b>OUTPUT</b>   |   |             |      |      |      |               |
| Collector emitter leakage current   | $V_{CE} = 20\text{ V}$                  | $I_{CEO}$   |      |      | 100  | nA            |
| Collector emitter capacitance   | $V_{CE} = 5\text{ V}, f = 1\text{ MHz}$ | $C_{CE}$    |      | 2.8  |      | pF            |
| Thermal resistance  |   | $R_{thja}$  |      | 500  |      | K/W           |
| <b>COUPLER</b>  |   |             |      |      |      |               |
| Collector emitter saturation voltage  | $I_F = 20\text{ mA}, I_C = 1\text{ mA}$ | $V_{CEsat}$ |      | 0.1  | 0.4  | V             |
| Coupling capacitance  | $f = 1\text{ MHz}$                      | $C_C$       |      | 1    |      | pF            |

**Note**

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.


| CURRENT TRANSFER RATIO ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |  |        |      |      |      |      |
|---|--|--------|------|------|------|------|
| PARAMETER   | TEST CONDITION                           | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| Current transfer ratio  | $I_F = 5\text{ mA}, V_{CC} = 5\text{ V}$ | CTR    | 50   |      | 300  | %    |

| <b>SWITCHING CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |   |           |      |      |      |               |
|---|---|-----------|------|------|------|---------------|
| PARAMETER   | TEST CONDITION  | SYMBOL    | MIN. | TYP. | MAX. | UNIT          |
| <b>NON-SATURATED</b>  |   |           |      |      |      |               |
| Rise time   | $I_C = 2\text{ mA}$ , $V_{CC} = 10\text{ V}$ , $R_L = 100\text{ }\Omega$  | $t_r$     |      | 4    |      | $\mu\text{s}$ |
| Fall time   | $I_C = 2\text{ mA}$ , $V_{CC} = 10\text{ V}$ , $R_L = 100\text{ }\Omega$  | $t_f$     |      | 3    |      | $\mu\text{s}$ |
| Turn-on time  | $I_C = 2\text{ mA}$ , $V_{CC} = 10\text{ V}$ , $R_L = 100\text{ }\Omega$  | $t_{on}$  |      | 5    |      | $\mu\text{s}$ |
| Turn-off time   | $I_C = 2\text{ mA}$ , $V_{CC} = 10\text{ V}$ , $R_L = 100\text{ }\Omega$  | $t_{off}$ |      | 4    |      | $\mu\text{s}$ |
| <b>SATURATED</b>  |   |           |      |      |      |               |
| Rise time   | $I_F = 16\text{ mA}$ , $V_{CC} = 5\text{ V}$ , $R_L = 1.9\text{ k}\Omega$ | $t_r$     |      | 15   |      | $\mu\text{s}$ |
| Fall time   | $I_F = 16\text{ mA}$ , $V_{CC} = 5\text{ V}$ , $R_L = 1.9\text{ k}\Omega$ | $t_f$     |      | 0.5  |      | $\mu\text{s}$ |
| Turn-on time  | $I_F = 16\text{ mA}$ , $V_{CC} = 5\text{ V}$ , $R_L = 1.9\text{ k}\Omega$ | $t_{on}$  |      | 1    |      | $\mu\text{s}$ |
| Turn-off time   | $I_F = 16\text{ mA}$ , $V_{CC} = 5\text{ V}$ , $R_L = 1.9\text{ k}\Omega$ | $t_{off}$ |      | 30   |      | $\mu\text{s}$ |



isfh6916\_01

Fig. 1 - Switching Operation (without Saturation)



isfh6916\_02


Fig. 2 - Switching Operation (with Saturation)

| <b>SAFETY AND INSULATION RATINGS</b>                 |                |            |      |           |      |                    |
|--|----------------|------------|------|-----------|------|--------------------|
| PARAMETER  | TEST CONDITION | SYMBOL     | MIN. | TYP.      | MAX. | UNIT               |
| Climatic classification (according to IEC 68 part 1) |                |            |      | 55/100/21 |      |                    |
| Comparative tracking index                           |                | CTI        | 175  |           | 399  |                    |
| Peak transient overvoltage                           |                | $V_{IOTM}$ | 6000 |           |      | V                  |
| Peak insulation voltage                              |                | $V_{IORM}$ | 707  |           |      | V                  |
| Safety rating - power output                         |                | $P_{SO}$   |      |           | 350  | mW                 |
| Safety rating - input current                        |                | $I_{SI}$   |      |           | 150  | mA                 |
| Safety rating - temperature                          |                | $T_{SI}$   |      |           | 175  | $^{\circ}\text{C}$ |
| Creepage distance                                    |                |            | 5    |           |      | mm                 |
| Clearance distance                                   |                |            | 5    |           |      | mm                 |

**Note**


- As per IEC 60747-5-2, § 7.4.3.8.1, this optocoupler is suitable for “safe electrical insulation” only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.

**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)




isfh6916\_03

Fig. 3 - Diode Forward Voltage vs. Forward Current




isfh6916\_06

Fig. 6 - Collector Current vs. Collector Emitter Saturation Voltage




isfh6916\_04

Fig. 4 - Collector Current vs. Collector Emitter Voltage




isfh6916\_07

Fig. 7 - Normalized Output Current vs. Ambient Temperature




isfh6916\_05

Fig. 5 - Collector to Emitter Dark Current vs. Ambient Temperature




isfh6916\_09

Fig. 8 - Current Transfer Ratio vs. Forward Current




isfh6916\_10

Fig. 9 - Switching Time vs. Load Resistance



isfh6916\_11

Fig. 10 - Switching Time vs. Load Resistance




isfh6916\_12


Fig. 11 - Switching Time Measurement



PACKAGE DIMENSIONS in millimeters



PACKAGE MARKING





## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.