

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → End Stops

General Information

Extended Product Type:	BADH
Product ID:	1SNA116900R2700
EAN:	3472591169003
Catalog Description:	BADH End Stops - Grey
Long Description:	- Give efficient support to the SNA double or triple deck or power terminal blocks assemblies thanks to the BADH double gripping rail contact, - Ease the assemblies identification with SNA markers and label holders.

Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	12 mm
Product Net Height:	55 mm
Product Net Depth / Length:	60 mm
Product Net Weight:	20 g

Technical

Spacing:	12 mm
Function:	End Stops
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Recommended Screw Driver:	5.5 mm
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m
Suitable For:	D1.5/6.D2.ADO D1.5/6.D2.ADO.NF D1/5.C4.ADO D1/5.D2.ADO D120/42.AF D120/42.FF D120/42.FF.Ex D150/31.D10 D185/55.AF

D185/55.FF
D185/55.FF.Ex
D2.5/5.A.L.L
D2.5/5.A.LL.L
D2.5/5.A.LLP.L
D2.5/5.A.N.L
D2.5/5.A.NL.L
D2.5/5.A.NLP.L
D2.5/5.A.NTLP.L
D2.5/5.D2.ADO
D2.5/5.D2.L
D2.5/5.DD.L
D2.5/5.DE.L
D2.5/5.DE1.D.L
D2.5/5.DE1.L
D2.5/5.DE2.D2.L
D2.5/5.DE2.L
D2.5/5.DL.L
D2.5/5.L.L
D2.5/5.LL.L
D2.5/5.LLP.L
D2.5/5.N.L
D2.5/5.NL.L
D2.5/5.NLP.L
D2.5/5.NTLP.L
D2.5/5.T1.L
D2.5/5.T1.P.L
D2.5/5.T3.L
D2.5/5.T3.P.L
D2.5/6.D
D2.5/6.DA
D2.5/6.DAL
D2.5/6.DL
D2.5/6.DP
D240/36.D10
D300/55.FF
D300/55.FF.Ex
D35/16.2L
D35/16.NT.L
D35/16.P.2L
D35/27.AF
D35/27.FF
D35/27.FF.Ex
D4/6.A.LL
D4/6.A.NLP
D4/6.A.NTLP
D4/6.D1.P.ADO
D4/6.D2.ADO
D4/6.L
D4/6.LL
D4/6.LLP

D4/6.NL
D4/6.NLP
D4/6.NTLP
D4/6.P.T1
D4/6.T
D4/6.T3.P
D4/8.D2.P.SF
D6/8.D2.ADO
D70/22
D70/22.P
D70/32.AF
D70/32.FF
D70/32.FF.Ex
D95/26
D95/26.P
DBL
M120/35.AF
M120/35.F
M120/35.FF
M300/42.AF
M300/42.F
M300/42.FF
M35/16.2A.2G
M35/26.AF
M35/26.F
M35/26.FF
M4/6.D1
M4/6.D2
M4/6.D2.2S2
M4/6.D2.NC
M4/6.D2.S1R
M4/6.D2.SB
M4/6.D2.SNBT
M4/6.D2.SNBT.NC
M4/6.DD
M4/6.DE
M4/6.DL
M4/6.DN
M4/7.D
M4/8.D2.SF
M4/8.D2.SF.NC
M6/8.D
M6/8.D2.NC
M70/31.AF
M70/31.F
M70/31.FF
MA2.5/5.D1
MA2.5/5.D2
MA2.5/5D-2CPE
RGW25-M5
RGW25-M6

RGW6-R1
RGW6-ST-1

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

RoHS Information: 1SND230479F0206

Classifications

Object Classification Code: X

E-number: 4029083

ETIM 4: EC001041 - End bracket for terminal block

ETIM 5: EC001041 - End bracket for terminal block

ETIM 6: EC001041 - End bracket for terminal block

Container Information

Package Level 1 Units: 50 piece

Package Level 1 Width: 176 mm

Package Level 1 Depth / Length: 200 mm

Package Level 1 Height: 75 mm

Package Level 1 Gross Weight: 1 kg

Package Level 1 EAN: 3472591169003

Package Level 2 Units: 450 piece

Package Level 3 Units: 10800 piece

Product Packing Type: Box



