

Tinned Annealed Copper Equipment Wires

multicomp PRO

**RoHS
Compliant**



RoHS Compliant 10

Description

PVC insulated equipment wires to defence standard 61 - 12 part 6 type 2 also comply with the requirements of BS4808 class 2. The maximum recommended operating temperature for these wires is 85°C. Defence standard current ratings quoted below will give a 15°C temperature rise at an ambient temperature of 70°C for single wires freely ventilated. Commercial ratings are suggested for use at 25°C ambient. The temperature range is -15°C to 85°C, the upper temperature is the temperature at the conductor due to a combination of ambient and temperature rise due to current flow. The lower temperature is for the product in static mode.

Specification Table

Area	Conductor	No. of Strands × Size	Max. Working Voltage (kV r.m.s)	Nominal Current Rating (A)	Insulation	Nominal Overall Diameter	Insulation Thickness	Ambient Temperature (°C)	Resistance at 20°C (Ω/kM)
7/0.2 (0.22 mm ²) type 2	Tinned annealed copper wire	7 × 0.2	1	1.4	PVC	1.2	0.3	1.4A at 70°C 2A at 25°C	88

Dimensions : Millimetres

Part Number Table

Description	Part Number
Equipment Wire, 7/0.2mm White, 100m	MCP00015
Equipment Wire 7/0.2mm Grey, 100m	MCP00016
Equipment Wire 7/0.2mm Violet, 100m	MCP00017
Equipment Wire 7/0.2mm Blue, 100m	MCP00018
Equipment Wire, 7/0.2mm Green, 100m	MCP00019
Equipment Wire 7/0.2mm Yellow, 100m	MCP00020
Equipment Wire 7/0.2mm Orange, 100m	MCP00021
Equipment Wire 7/0.2mm Red, 100m	MCP00022
Equipment Wire 7/0.2mm Brown, 100m	MCP00023
Equipment Wire 7/0.2mm Black, 100m	MCP00024

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO