


# LC1K0610Q7

TeSys K contactor - 3P - AC-3  $\leq$  440 V 6 A - 1  
NO aux. - 380...400 V AC coil

Product availability : Non-Stock - Not normally stocked in distribution facility



## Main

|                           |               |
|---------------------------|---------------|
| Range                     | TeSys         |
| Product or component type | Contacteur    |
| Product name              | TeSys K       |
| Device short name         | LC1K          |
| Device application        | Control       |
| Contacteur application    | Motor control |

## Complementary

|  |   |
|--|---|
| Utilisation category                   | AC-3<br>AC-4  |
| Poles description                      | 3P  |
| Power pole contact composition         | 3 NO  |
| [Ue] rated operational voltage         | Power circuit 690 V AC 50/60 Hz<br>Signalling circuit $\leq$ 690 V AC 50/60 Hz  |
| [Ie] rated operational current         | 6 A $\leq$ 440 V AC AC-3 power circuit  |
| Control circuit type                   | AC 50/60 Hz   |
| [Uc] control circuit voltage           | 380...400 V AC 50/60 Hz   |
| Motor power kW                         | 1.5 kW 220...230 V AC 50/60 Hz AC-3<br>2.2 kW 380...415 V AC 50/60 Hz AC-3<br>3 kW 440 V AC 50/60 Hz AC-3<br>3 kW 480 V AC 50/60 Hz AC-3<br>3 kW 500...600 V AC 50/60 Hz AC-3<br>3 kW 660...690 V AC 50/60 Hz AC-3<br>1.5 kW 400 V AC 50/60 Hz AC-4 |
| Auxiliary contact composition          | 1 NO  |
| [Uimp] rated impulse withstand voltage | 8 kV  |
| Overvoltage category                   | III   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|  |  |
|--|--|
| [I <sub>th</sub> ] conventional free air thermal current | 20 A 122 °F (50 °C) power circuit<br>10 A 122 °F (50 °C) signalling circuit  |
| I <sub>rms</sub> rated making capacity                   | 110 A AC power circuit NF C 63-110<br>110 A AC power circuit IEC 60947<br>110 A AC signalling circuit IEC 60947  |
| Rated breaking capacity                                  | 110 A 415 V IEC 60947<br>110 A 440 V IEC 60947<br>80 A 500 V IEC 60947<br>110 A 220...230 V IEC 60947<br>110 A 380...400 V IEC 60947<br>70 A 660...690 V IEC 60947   |
| [I <sub>cw</sub> ] rated short-time withstand current    | 90 A 122 °F (50 °C) - 1 s power circuit<br>85 A 122 °F (50 °C) - 5 s power circuit<br>80 A 122 °F (50 °C) - 10 s power circuit<br>60 A 122 °F (50 °C) - 30 s power circuit<br>45 A 122 °F (50 °C) - 1 min power circuit<br>40 A 122 °F (50 °C) - 3 min power circuit<br>20 A 122 °F (50 °C) - >= 15 min power circuit<br>80 A - 1 s signalling circuit<br>90 A - 500 ms signalling circuit<br>110 A - 100 ms signalling circuit  |
| Associated fuse rating                                   | 25 A gG <= 440 V power circuit<br>25 A aM power circuit<br>10 A gG signalling circuit IEC 60947<br>10 A gG signalling circuit VDE 0660   |
| Average impedance  | 3 mOhm - I <sub>th</sub> 20 A 50 Hz power circuit  |
| [U <sub>i</sub> ] rated insulation voltage               | Power circuit 600 V UL 508<br>Power circuit 690 V IEC 60947-4-1<br>Signalling circuit 690 V IEC 60947-4-1<br>Signalling circuit 690 V IEC 60947-5-1<br>Signalling circuit 600 V UL 508<br>Power circuit 600 V CSA C22.2 No 14<br>Signalling circuit 600 V CSA C22.2 No 14  |
| Insulation resistance                                    | > 10 MOhm signalling circuit   |
| Inrush power in VA                                       | 30 VA 68 °F (20 °C))   |
| Hold-in power consumption in VA                          | 4.5 VA 68 °F (20 °C))  |
| Heat dissipation   | 1.3 W  |
| Control circuit voltage limits                           | Operational 0.8...1.15 U <sub>c</sub> 122 °F (50 °C))<br>Drop-out 0.2...0.75 U <sub>c</sub> 122 °F (50 °C))  |
| Connections - terminals                                  | screw clamp terminals 1 0.00...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> )solid<br>screw clamp terminals 1 0.00...0.01 in <sup>2</sup> (0.75...4 mm <sup>2</sup> )flexible without cable end<br>screw clamp terminals 1 0.00...0.00 in <sup>2</sup> (0.34...2.5 mm <sup>2</sup> )flexible with cable end<br>screw clamp terminals 2 0.00...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> )solid<br>screw clamp terminals 2 0.00...0.01 in <sup>2</sup> (0.75...4 mm <sup>2</sup> )flexible without cable end<br>screw clamp terminals 2 0.00...0.00 in <sup>2</sup> (0.34...1.5 mm <sup>2</sup> )flexible with cable end |
| Maximum operating rate                                   | 3600 cyc/h   |
| Auxiliary contacts type                                  | Instantaneous 1 NO   |
| Signalling circuit frequency                             | <= 400 Hz  |
| Minimum switching current                                | 5 mA signalling circuit  |
| Minimum switching voltage                                | 17 V signalling circuit  |
| Mounting support   | Plate<br>Rail  |
| Tightening torque  | 11.51 lbf.in (1.3 N.m) screw clamp terminals Philips No 2<br>11.51 lbf.in (1.3 N.m) screw clamp terminals flat Ø 6 mm  |
| Operating time   | 10...20 ms coil de-energisation and NO opening<br>10...20 ms coil energisation and NO closing  |
| Safety reliability level                                 | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1<br>B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1   |
| Non overlap distance                                     | 0.02 in (0.5 mm)   |
| Mechanical durability                                    | 10 Mcycles   |
| Electrical durability                                    | 1.3 Mcycles 6 A AC-3 <= 440 V  |
| Mechanical robustness                                    | Shocks contactor closed, on X axis10 Gn for 11 ms IEC 60068-2-27<br>Shocks contactor closed, on Y axis15 Gn for 11 ms IEC 60068-2-27<br>Shocks contactor closed, on Z axis15 Gn for 11 ms IEC 60068-2-27<br>Shocks contactor opened, on X axis6 Gn for 11 ms IEC 60068-2-27  |

Shocks contactor opened, on Y axis 10 Gn for 11 ms IEC 60068-2-27  
 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27  
 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6  
 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6

|            |                       |
|------------|-----------------------|
| Height     | 2.28 in (58 mm)       |
| Width      | 1.77 in (45 mm)       |
| Depth      | 2.24 in (57 mm)       |
| Net weight | 0.40 lb(US) (0.18 kg) |

## Environment

|                                     |  |
|-------------------------------------|--|
| Standards                           | BS 5424<br>IEC 60947<br>NF C 63-110<br>VDE 0660                    |
| Product certifications              | CSA<br>UL  |
| IP degree of protection             | IP2x VDE 0106  |
| Protective treatment                | TC IEC 60068<br>TC DIN 50016                                       |
| Ambient air temperature for storage | -58...176 °F (-50...80 °C)   |
| Operating altitude                  | 6561.68 ft (2000 m) without  |
| Flame retardance                    | V1 UL 94<br>Requirement 2 NF F 16-101<br>Requirement 2 NF F 16-102 |

## Ordering and shipping details

|                   |                                   |
|-------------------|-----------------------------------|
| Category          | 22326 - CTR,K-LINE,AC,OPEN,NONREV |
| Discount Schedule | I12                               |
| GTIN              | 00785901423515                    |
| Returnability     | No                                |
| Country of origin | FR                                |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.       |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End of Life Information</a>  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|