

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	GVAE
Product or component type	Auxiliary contact block
Product compatibility	GV2L GV2P GV2RT GV3P GV2LE GV3L LS1D323 GV2ME
Mounting location	Front side
Pole contact composition	2 NO
Connections - terminals	spring terminals 2 0.00...0.00 in ² (0.75...1.5 mm ²)flexible without cable end
Quantity per set	Set of 10

Complementary

[Ui] rated insulation voltage	300 V UL 508 300 V CSA C22.2 No 14 250 V IEC 60947-1
[Ue] rated operational voltage	24...240 V AC 24...60 V DC
[Ith] conventional free air thermal current	2.5 A
Protection type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	120 VA 110...120 V AC-15 100000 cycles 120 VA 230...240 V AC-15 100000 cycles

	48 VA 24 V AC-15 100000 cycles 60 VA 48 V AC-15 100000 cycles
Rated operational power in W	15 W 48 V DC-13 100000 cycles 24 W 24 V DC-13 100000 cycles 9 W 60 V DC-13 100000 cycles
Height	0.51 in (13 mm)
Width	1.75 in (44.5 mm)
Depth	1.24 in (31.5 mm)
Net weight	0.11 lb(US) (0.05 kg)

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901494928
Returnability	No
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------