


Air solenoid valve VUVS-L30-M52-MD-G38-F8

FESTO

Part number: 575602



Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/2, monostable |
| Material of screws | Steel, nickel-plated |
| Lap | Overlap |
| Actuation type | Electrical |
| Valve size | 31 mm |
| Standard nominal flow rate | 2300 l/min |
| Pneumatic working port | G3/8 |
| Operating pressure | 2.5 bar ... 10 bar |
| Design | Piston gate valve |
| Reset method | Mechanical spring |
| Certification | c UL us - Recognized (OL) |
| Nominal width | 9.4 mm |
| Type code | VUVS |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Non-detenting Detenting |
| Type of control | Pilot-controlled |
| Pilot air supply port | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991035 |
| b-value | 0.4 |
| C value | 9.9 l/sbar |
| Switching time off | 62 ms |
| On switching time | 17 ms |
| Max. positive test pulse with 0 signal | 2000 µs |
| Max. negative test pulse on 1 signal | 3600 µs |
| Certificate issuing authority | DNVGL-TAA000011J |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Temperature of medium | -10 °C ... 60 °C |

| Feature | Value |
|---------------------------|---|
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 450 g |
| Type of mounting | Optionally: With through-hole On terminal strip |
| Venting hole connection | Not ducted |
| Pilot exhaust air port 84 | M5 |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | G3/8 |
| Pneumatic connection 3 | G3/8 |
| Pneumatic connection 4 | G3/8 |
| Pneumatic connection 5 | G3/8 |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR |
| Housing material | Die-cast aluminum Painted |
| Piston slide material | Wrought aluminum alloy |