



## Schneider Electric Relays


200 N. Martingale Rd., Suite 1000

Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: [relays@schneider-electric.com](mailto:relays@schneider-electric.com) • Web site: [www.serelays.com](http://www.serelays.com)

ITEM # 788XBXR69C-120A, 788 POWER RELAYS / DPDT, 10 AMP RATING



[SPECIFICATIONS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#)

### Specifications

Check Inventory [Check Distributor Inventory](#)

Status Standard

Legacy Part No. 788XBXR69C-120A

Contact Configuration DPDT

Thermal (Carrying) Current 10 A

Terminal Style Plug-in

Coil Resistance (Ohms) 1700 Ohm

Load Type Standard

Contact Materials Silver Alloy with Gold Flash

Cover Options Plain Cover

Maximum Switching Voltages UL: 300 VAC/125 VDC

<b>Switching Current at Voltage (AC, Resistive)</b>	IEC: 10 A at 250 VAC 50/60 Hz UL: 10 A at 277 VAC 50/60 Hz
---	---

<b>Switching Current at Voltage (DC, Resistive)</b>	IEC: 10 A at 28 VDC UL: 10 A at 30 VDC
---	---

<b>Current Rating with Magnetic Blowout - Code 69</b>	UL: 3 A at 150 VDC
---	--------------------

<b>Minimum Switching Requirement</b>	10 mA at 17 VDC
--------------------------------------	-----------------

<b>Features</b>	LED, Blow-out magnet, Mechanical flag indicator
-----------------	---

#### California Proposition 65 Warning



**WARNING:** This product can expose you to chemicals including:  
**Substance 1:** Nickel compounds, which is known to the State of California to cause cancer.  
**Substance 2:** DIDP, which is known to the State of California to cause birth defects or other reproductive harm.  
 For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

#### Coil Characteristics

<b>Operating Range - % of Nominal (AC)</b>	85 to 110 %
--	-------------

<b>Operating Range - % of Nominal (DC)</b>	80 to 110 %
--	-------------

<b>Average Consumption (AC / VA)</b>	3 VA
--------------------------------------	------

<b>Drop-out Voltage Threshold (AC)</b>	15 %
--	------

#### Performance Characteristics

<b>Electrical Life (UL508), Operations at Rated Current (Resistive)</b>	100000
---	--------

<b>Mechanical Life, Unpowered</b>	5000000
-----------------------------------	---------

<b>Operating Time (Response Time)</b>	20 ms
---------------------------------------	-------

<b>Dielectric Strength - Between Coil and Contact (AC)</b>	2500 V(rms)
--	-------------

<b>Dielectric Strength - Between Poles (AC)</b>	2000 V(rms)
---	-------------

#### Environment

<b>Product Certifications</b>	UL (E164862) CSA (225619 Class 3211-07) CE RoHs
-------------------------------	--

<b>Vibration Resistance - Operational</b>	3 g-n at 35-150 Hz
---	--------------------

<b>Shock Resistance</b>	10 g-n
-------------------------	--------

<b>Degree of Protection</b>	IP 40
-----------------------------	-------

<b>Weight</b>	2.93 oz 83 g
---------------	-----------------