



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 10

SDS No. : 208471
V003.3

LOCTITE ARAX 96S 4C 0.7MM G known as 96S ARAX SS 4C

Revision: 28.05.2015
printing date: 04.04.2020
Replaces version from: 22.11.2013

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE ARAX 96S 4C 0.7MM G known as 96S ARAX SS 4C

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Solder Wire

1.3. Details of the supplier of the safety data sheet

Henkel Belgium N.V.
Esplanade 1
1020 Brussels

Belgium

Phone: +32 (2) 421 2711
Fax-no.: +32 (2) 420 7025

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation

Category 2

H315 Causes skin irritation.

Serious eye irritation

Category 2

H319 Causes serious eye irritation.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Warning

Hazard statement:

H315 Causes skin irritation.
H319 Causes serious eye irritation.

Precautionary statement: P261 Avoid breathing fume.
Prevention

Precautionary statement: P302+P352 IF ON SKIN: Wash with plenty of water.
Response P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

Avoid breathing fumes given out during soldering.

After handling solder wash hands with soap and water before eating, drinking or smoking.

Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).

Keep out of reach of children.

Do not heat above 500 °C

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Tin 7440-31-5	231-141-8 01-2119486474-28	>= 90- < 100 %	
Silver 7440-22-4	231-131-3	>= 1- < 5 %	
Ammonium hydrogendifluoride 1341-49-7	215-676-4 01-2119489180-38	>= 0,1- < 1 %	Skin Corr. 1B H314 Acute Tox. 3; Oral H301

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Flush eyes with plenty of water for at least 5 minutes. If irritation persists seek medical attention.

Ingestion:

Do not induce vomiting.

Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Flux fumes may irritate the nose, throat and lungs and may after prolonged/repeated exposure give an allergic reaction (asthma).

EYE: Irritation, conjunctivitis.

SKIN: Redness, inflammation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Fine water spray

Extinguishing media which must not be used for safety reasons:

Do not use water on fires where molten metal is present.

5.2. Special hazards arising from the substance or mixture

High temperatures may produce heavy metal dust, fumes or vapours.

The flux medium will give rise to irritating fumes.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Additional information:

The product itself does not burn. Any fire extinguishing action should be appropriate to the surroundings.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Scrape up spilled material and place in a closed container for disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Extraction is necessary to remove fumes evolved during reflow.

When using do not eat, drink or smoke.

Wash hands before breaks and immediately after handling the product.

Avoid breathing fumes given out during soldering.

Do not heat above 500 °C

See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.

Do not eat, drink or smoke while working.

After handling solder wash hands with soap and water before eating, drinking or smoking.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Store in a cool, dry place.

7.3. Specific end use(s)

Solder Wire

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Tin 7440-31-5 [TIN (INORGANIC COMPOUNDS AS SN)]		2	Time Weighted Average (TWA):	Indicative	ECTLV
Silver 7440-22-4 [SILVER (METALLIC)]		0,1	Time Weighted Average (TWA):		EH40 WEL
Silver 7440-22-4 [SILVER, METALLIC]		0,1	Time Weighted Average (TWA):	Indicative	ECTLV
Ammonium hydrogendifluoride 1341-49-7 [FLOURIDE (INORGANIC, AS F)]		2,5	Time Weighted Average (TWA):		EH40 WEL
Ammonium hydrogendifluoride 1341-49-7 [FLUORIDES, INORGANIC]		2,5	Time Weighted Average (TWA):	Indicative	ECTLV

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
1341-49-7	aqua (freshwater)					1,3 mg/L	
1341-49-7	soil				22 mg/kg		
1341-49-7	STP					76 mg/L	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Tin 7440-31-5	Workers	Dermal	Acute/short term exposure - systemic effects		133,3 mg/kg	
Tin 7440-31-5	Workers	Inhalation	Acute/short term exposure - systemic effects		11,75 mg/m3	
Tin 7440-31-5	Workers	Dermal	Long term exposure - systemic effects		133,3 mg/kg	
Tin 7440-31-5	Workers	Inhalation	Long term exposure - systemic effects		11,75 mg/m3	
Tin 7440-31-5	general population	Dermal	Acute/short term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	general population	Inhalation	Acute/short term exposure - systemic effects		3,476 mg/m3	
Tin 7440-31-5	general population	oral	Acute/short term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	general population	Dermal	Long term exposure - systemic effects		80 mg/kg	
Tin 7440-31-5	general population	Inhalation	Long term exposure - systemic effects		3,476 mg/m3	
Tin 7440-31-5	general population	oral	Long term exposure - systemic effects		80 mg/kg	
1341-49-7	Workers	Inhalation	Acute/short term exposure - local effects		3,8 mg/m3	
1341-49-7	Workers	Inhalation	Long term exposure - systemic effects		2,3 mg/m3	
1341-49-7	general population	oral	Long term exposure - systemic effects		0,015 mg/kg bw/day	
1341-49-7	general population	oral	Acute/short term exposure - systemic effects		0,015 mg/kg bw/day	
1341-49-7	general population	Inhalation	Long term exposure - systemic effects		0,045 mg/m3	

Biological Exposure Indices:

None

8.2. Exposure controls:**Engineering controls:**

Extraction is necessary to remove fumes evolved during reflow.

Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction.

Ensure good ventilation/extraction.

Respiratory protection:

In case of aerosol formation, we recommend wearing of appropriate respiratory protection equipment with ABEK P2 filter. This recommendation should be matched to local conditions.

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	solid material
	grey
Odor	None
Odour threshold	No data available / Not applicable
pH	Not applicable
Initial boiling point	Not determined
Flash point	Not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	Not applicable
Density (25 °C (77 °F))	7,5 g/cm ³
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	221 - 240 °C (429.8 - 464 °F)
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

No decomposition if stored and applied as directed.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

Fumes evolved at soldering temperatures will irritate the nose, throat and lungs.

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Ammonium hydrogendifluoride 1341-49-7	LD50	130 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Skin corrosion/irritation:

Hazardous components CAS-No.	Result		Exposure time	Species	Method
Silver 7440-22-4	slightly irritating			rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result		Exposure time	Species	Method
Silver 7440-22-4	slightly irritating			rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Ammonium hydrogendifluoride 1341-49-7	negative	bacterial reverse mutation assay (e.g Ames test)	no data		

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Ammonium hydrogendifluoride 1341-49-7	LC50	365 mg/l	Fish	96 h	Brachydanio rerio (new name: Danio rerio)	OECD Guideline 203 (Fish, Acute Toxicity Test)

12.2. Persistence and degradability**Persistence and Biodegradability:**

The product is not biodegradable.

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

The product is insoluble and sinks in water.

Bioaccumulative potential:

No data available.

Bioaccumulative potential:

Octanol/Water distribution coefficient: Not applicable

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Ammonium hydrogendifluoride 1341-49-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Wherever possible unwanted solder alloy should be recycled for recovery of metal.
Otherwise dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Dispose of as unused product.

Waste code

06 04 05 - wastes containing other heavy metals

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packaging group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3,0 %

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

National regulations/information (Great Britain):**Remarks**

The Health & Safety at Work Act 1974.
The Control of Substances Hazardous to Health Regulations. L5:General
Approved Code of Practice to the COSHH Regulations. HS(G)97:A Step by Step
Guide to the COSHH Regulations. HS(G)193: COSHH essentials: Easy steps to
control chemicals.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H301 Toxic if swallowed.

H314 Causes severe skin burns and eye damage.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.