



Main

| | |
|--------------------------------|-------------------|
| Range | TeSys |
| Product name | TeSys CAK |
| Product or component type | Control relay |
| Device short name | CA2K |
| Contacteur application | Control circuit |
| Utilisation category | DC-13 AC-15 |
| Pole contact composition | 3 NO + 1 NC |
| [Ue] rated operational voltage | ≤ 690 V ≤ 400 Hz |
| Control circuit type | AC at 50/60 Hz |
| [Uc] control circuit voltage | 230 V AC 50/60 Hz |

Complementary

| | |
|---|--|
| [Ith] conventional free air thermal current | 10 A (at 50 °C) |
| Irms rated making capacity | 110 A conforming to IEC 60947 |
| Associated fuse rating | 10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660 |
| [Ui] rated insulation voltage | 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C 690 V conforming to BS 5424 600 V conforming to CSA C22.2 No 14 600 V conforming to UL 508 690 V conforming to NF C 20-040 |
| Mounting support | Rail Plate |
| Connections - terminals | Screw clamp terminals 1 cable(s) 1.5...4 mm ² solid Screw clamp terminals 2 cable(s) 1.5...4 mm ² solid Screw clamp terminals 1 cable(s) 0.75...4 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.75...4 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.34...1.5 mm ² flexible with cable end |

| | |
|---------------------------------|---|
| | Screw clamp terminals 2 cable(s) 0.34...1.5 mm ² flexible without cable end |
| Tightening torque | 0.8 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm 0.8 N.m - on screw clamp terminals - with screwdriver Philips No 26 mm |
| Control circuit voltage limits | Drop-out: 0.2...0.75 U _c (at <50 °C) Operational: 0.8...1.15 U _c (at <50 °C) |
| Operating time | 10...20 ms coil de-energisation and NO opening 10...20 ms coil energisation and NO closing 15...25 ms coil de-energisation and NC closing 5...15 ms coil energisation and NC opening |
| Mechanical durability | 10 Mcycles |
| Maximum operating rate | 3600 cyc/h |
| Immunity to microbreaks | 2 ms |
| Inrush power in VA | 30 VA (at 20 °C) |
| Hold-in power consumption in VA | 4.5 VA (at 20 °C) |
| Heat dissipation | 1.3 W |
| Minimum switching voltage | 17 V |
| Minimum switching current | 5 mA |
| Non overlap distance | 0.5 mm |
| Insulation resistance | > 10 MOhm |
| Height | 58 mm |
| Width | 45 mm |
| Depth | 57 mm |
| Net weight | 0.235 kg |

Environment

| | |
|---------------------------------------|---|
| Standards | BS 5424 IEC 60947 VDE 0660 NF C 63-110 EN 60335-1 |
| Product certifications | UL CSA |
| IP degree of protection | IP20 |
| Protective treatment | TC conforming to IEC 60068 TC conforming to DIN 50016 |
| Ambient air temperature for operation | -25...50 °C |
| Ambient air temperature for storage | -50...80 °C |
| Operating altitude | 2000 m without |
| Flame retardance | V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102 |
| Mechanical robustness | Vibrations contactor open: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6 Vibrations contactor closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

| | |
|---------------------|---|
| Circularity Profile | End of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
