



Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX4FJ
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F400
Control circuit type	DC low consumption
[Uc] control circuit voltage	24 V DC
Average resistance	2.5 Ohm inrush at 20 °C 558 Ohm holding at 20 °C
Inductance of closed circuit	56 H
Operating time	45...60 ms opening 50...60 ms closing
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 55 °C

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.2...0.35 Uc (at 55 °C) Operational: 0.85...1.1 Uc (at 55 °C)
Inrush power in W	1000 W (at 20 °C)
Hold-in power consumption in W	6 W at 20 °C

Environment

Ambient air temperature for operation	-5...55 °C
Net weight	0.97 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information