



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Differential thermal overload relay
Device short name	LRD
Relay application	Motor protection
Product compatibility	LC1D18 LC1D12 LC1D32 LC1D25 LC1D38
Network type	DC AC
Thermal protection adjustment range	9...13 A
[Ui] rated insulation voltage	Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1

Complementary

Network frequency	0...400 Hz
Mounting support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
[I _{th}] conventional free air thermal current	5 A for signalling circuit
Permissible current	3 A at 120 V AC-15 for signalling circuit 0.22 A at 125 V DC-13 for signalling circuit
[U _e] rated operational voltage	690 V AC 0...400 Hz
[U _{imp}] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current 130 % of I _r on two phase, the last one at 0
Control type	Red push-button: stop

	Blue push-button: reset
Temperature compensation	-20...60 °C
Connections - terminals	Control circuit: spring terminals 1 cable(s) 1...2.5 mm ² solid without cable end Control circuit: spring terminals 1 cable(s) 1...2.5 mm ² flexible without cable end Power circuit: spring terminals 1 cable(s) 1.5...4 mm ² flexible without cable end Power circuit: spring terminals 1 cable(s) 1.5...4 mm ² flexible with cable end
Width	45 mm
Depth	66 mm
Net weight	0.14 kg

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-60...70 °C
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations: 6 Gn conforming to IEC 60068-2-6 Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	ATEX D 94/9/CE UL 508 EN 60947-5-1 IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-4-1 EN 60947-4-1
Product certifications	GOST BV RINA GL DNV LROS (Lloyds register of shipping) CSA CCC ATEX INERIS UL

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------