


PRODUCT-DETAILS

# PS1/60/16

## PS1/60/16 - Busbar



### General Information

Extended Product Type	PS1/60/16
Product ID	2CDL210001R1660
EAN	4016779516655
Catalog Description	PS1/60/16 - Busbar
Long Description	PS1/60/16 Busbar

### Ordering

EAN	4016779516655
Minimum Order Quantity	1 piece
Customs Tariff Number	85369010

### Dimensions

Product Net Width	20 mm
Product Net Height	17 mm
Product Net Length	1050 mm
Product Net Depth / Length	1050 mm
Product Net Weight	0.41 kg

### Container Information

Package Level 1 Units	20 piece
Package Level 1 Width	145 mm
Package Level 1 Height	45 mm
Package Level 1 Depth / Length	1070 mm
Package Level 1 Gross Weight	0.87 kg

## Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

## Additional Information

Accessory Type	Busbar
Color	Grey
Housing Material	Light grey, RAL 7035
Mounting Position	Any
Number of Phases	1
Overvoltage Category	III
Pollution Degree	2
Product Main Type	Busbars PS
Product Name	Busbar
Rated Cross-Section	16 mm <sup>2</sup>
Rated Frequency (f)	50 Hz 60 Hz DC
RoHS Date	20170228
Suitable For	S200 F200 DDA200
Suitable for Product Class	Miniature Circuit Breakers Residual Current Circuit Breakers Residual Current Circuit Breakers with Overcurrent Protection

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106930A8017
Declaration of Conformity - CE	2CDK446006D0403
Environmental Information	2CDU400029D0201
Instructions and Manuals	2CSC400002D0208
RoHS Information	2CDK440009K0203

## Classifications

ETIM 4	EC000215 - Phase busbar
ETIM 5	EC000215 - Phase busbar
ETIM 6	EC000215 - Phase busbar
ETIM 7	EC000215 - Phase busbar
Object Classification Code	W
UNSPSC	39121614
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
eClass	7.0 27371306

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs Accessories → Busbars and Accessories (IEC Range)

