

# GS1AN22

Auxiliary contacts, TeSys GS, 2NC + 2NO, instantaneous, left side mounting, for GS1-GS2 with front/right handle



## Main

Range of product	TeSys
Device short name	GS1AN
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Contacts type and composition	2 NO + 2 NC
Contact operation	Instantaneous
[I <sub>th</sub> ] conventional free air thermal current	20 A 104 °F (40 °C)
[I <sub>e</sub> ] rated operational current	1 A 220 V DC-13 10 A 230 V AC-15 12 A 127 V AC-15 4 A 48 V DC-13 6 A 440 V AC-15 8 A 400/415 V AC-15 1.2 A 110 V DC-13

## Complementary

Range compatibility	TeSys GS fuse-switch disconnectors
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-15
Switch rated current	200 A 60 A 600 A 630 A 315 A 400 A 800 A 250 A 125 A 1250 A 160 A 50 A 63 A 100 A
Fuse type	DIN NFC

	BS
Type of operating handle	Direct frontal External frontal Direct right side External right side
Net weight	0.52 lb(US) (0.238 kg)

### Ordering and shipping details

Category	22640-IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901367789
Returnability	No
Country of origin	FR

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------