


PRODUCT-DETAILS

TM40/24

TM40/24 Fail safe bell transformer



General Information

Extended Product Type	TM40/24
Product ID	2CSM228785R0802
EAN	8012542287858
Catalog Description	TM40/24 Fail safe bell transformer
Long Description	These transformers, with safety extremely-low voltage secondary (SELV), are suitable for driving loads that call for a discontinuous supply.

Ordering

EAN	8012542287858
Minimum Order Quantity	1 piece
Customs Tariff Number	85043121

Dimensions

Product Net Width	52.5 mm
Product Net Height	0.085 m
Product Net Length	65 mm
Product Net Depth / Length	0.065 m
Product Net Weight	0.450 kg

Container Information

Package Level 1 Units	4 piece
Package Level 1 Width	0.09 m
Package Level 1 Height	0.08 m
Package Level 1 Depth / Length	0.054 m
Package Level 1 Gross Weight	1.8 kg
Package Level 1 EAN	8012542287865

Environmental

RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
-------------	---

Additional Information

Options Provided	None
Output Current Maximum (I_{out})	3,33 A
Power Loss	Maximum 4 W
Power Supply	40 V·A
Primary Voltage	230 V
Product Main Type	TM
Product Name	Fail safe bell transformer
RoHS Date	25/06/2009 0.00.00
Secondary Current	Amperage 2 1.66 A Amperage 1 3.33 A
Secondary Voltage	1 12 V 2 24 V

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CSC000001D0202
Declaration of Conformity - CE	2CSC446001D2702
Instructions and Manuals	on the product body
RoHS Information	2CSC446004K0201

Classifications

ETIM 4	EC001547 - Bell transformer
ETIM 5	EC001547 - Bell transformer
ETIM 6	EC001547 - Bell transformer
ETIM 7	EC001547 - Bell transformer
Object Classification Code	T
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Command and Signalling devices → Bells and safety transformers

