

GS1AM211

Auxiliary contacts, TeSys GS, 2 C/O, early break, side mounting, for GS1 32 A with direct front/right handle



Main

Range of product	TeSys
Device short name	GS1AM
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Range compatibility	TeSys GS GS1D fuse-switch disconnecter
Contacts type and composition	2 C/O
Contact operation	Early-break
[I _{th}] conventional free air thermal current	16 A (at 40 °C)
[I _e] rated operational current	5 A at 127 V AC-15 4 A at 230 V AC-15 3 A at 400/415 V AC-15 2 A at 440 V AC-15 12 A at 24 V DC-13 2 A at 48 V DC-13 0.6 A at 110 V DC-13 0.4 A at 220 V DC-13

Complementary

Mechanical durability	1 Mcycles
Electrical durability	30000 cycles AC-15
Switch rated current	32 A
Fuse type	NFC DIN BS
Type of operating handle	Direct frontal
Mounting location	Right side
Net weight	0.07 kg

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------