

# GS1AN22G

Auxiliary contacts, TeSys GS, 2NC + 2NO, instantaneous, right side mounting, for GS2 with left handle



## Main

Range of product	TeSys
Device short name	GS1AN
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Contacts type and composition	2 NO + 2 NC
Contact operation	Instantaneous
[I <sub>th</sub> ] conventional free air thermal current	20 A (at 40 °C)
[I <sub>e</sub> ] rated operational current	1 A at 220 V DC-13 10 A at 230 V AC-15 12 A at 127 V AC-15 4 A at 48 V DC-13 6 A at 440 V AC-15 8 A at 400/415 V AC-15 1.2 A at 110 V DC-13

## Complementary

Range compatibility	TeSys GS fuse-switch disconnectors
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-15
Switch rated current	100 A 125 A 160 A 60 A 400 A 600 A 800 A 200 A 630 A 250 A 315 A 50 A 63 A 1250 A
Fuse type	DIN BS NFC

Type of operating handle	External left side
Net weight	0.252 kg

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------