

Multi-Conductor Low Capacitance (Belden 8103 Alternative) Cable

multicomp PRO



**RoHS
Compliant**

Application

An overall foil and braid screened cable used at high data rates for RS 232 and RS 422 applications.

Characteristics

Voltage Rating	: 300V
Temperature Rating	: -30°C to +80°C
Minimum Bending Radius	: 10 × overall diameter
Pair Identification	: Pair 1: White/Blue, Blue/White Pair 2: White/Orange, Orange/White Pair 3: White/Green, Green/White
Sheath Colour	: Grey

Cable Standards

EIA RS232, RS422

Construction

Conductor

Class 2 stranded tinned copper conductor

Insulation

Datalene® FPE (Foam Polyethylene)

Screen 1

Beldfoil® (Aluminium foil polyester tape)

Drain Wire

Tinned Copper

Screen 2

TCWB (Tinned Copper Wire Braid)

Sheath

PVC (Polyvinyl Chloride)

This product range is available on reels of 100m or per metre

Dimensions

No. of Pairs	AWG (No. of Strands)	Nominal Diameter of Strands mm	Nominal Overall Diameter mm	Nominal Weight kg/km
3	AWG24 (7)	0.032	7.18	58

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Multi-Conductor Low Capacitance (Belden 8103 Alternative) Cable



Electrical Characteristics

AWG (No. of Strands)	Capacitance		Velocity of Propagation %	Impedance Ω	Maximum Resistance of Conductor at 20°C Ω/km
	Conductor to Conductor pF/m	Conductor to Shield pF/m			
AWG24 (7)	41.01	72.18	78	100	78.74

Part Number Table

Description	Cable Length	Part Number
Multi-Conductor Low Capacitance Cable, (Belden 8103 Alternative), 3Pair, 24AWG, Grey	100m or per metre	PP002188

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

