

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Name of product Citrus-Cleaner Spray

1.2. Relevant identified uses of the substance or mixture and uses advised against Recommended intended purpose(s)

Technical Aerosols

1.3. Details of the supplier of the safety data sheet

Premier Farnell plc
150 Armley Road, Leeds, LS12 2QQ
+44 (0) 8701 202530

1.4. Emergency telephone number

+44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]

Hazard classes and Hazard categories	Hazard Statements Classification procedure
Aerosol 1	H222, H229
Skin Irrit. 2	H315
Eye Irrit. 2	H319
Skin Sens. 1	H317
STOT SE 3	H336
Aquatic Chronic 2	H411

Hazard Statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]



GHS02



GHS07



GHS09

Signal word

Danger

Hazard Statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary Statements

P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P264	Wash hands thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P272	Contaminated work clothing should not be allowed out of the workplace.
P273	Avoid release to the environment.
P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P304 + P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312	Call a POISON CENTRE or doctor/physician if you feel unwell.
P333 + P313 I	If skin irritation or rash occurs: Get medical advice/attention.
P337 + P313	If eye irritation persists: Get medical advice/attention.
P363	Wash contaminated clothing before reuse.
P403 + P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P410 + P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501	Dispose of contents/container to hazardous or special waste collection point.

Hazardous ingredients for labeling

(R)-p-mentha-1,8-diene

2.3. Other hazards

Information pertaining to special dangers for human and environment

In extensive use, formation of flammable / explosive vapour-air mixture is possible.

Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

SECTION 3: Composition/ information on ingredients

3.1. Substances

not applicable

3.2. Mixtures

Description

Preparation based on propellant mixture.

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
67-63-0	200-661-7	propan-2-ol	75 - 99,99	Flam. Liq. 2, H225 / Eye Irrit. 2, H319 / STOT SE 3, H336
5989-27-5	227-813-5	(R)-p-mentha-1,8-diene	10 < 25	Flam. Liq. 3, H226 / Skin Irrit. 2, H315 / Skin Sens. 1, H317 / Aquatic Acute 1, H400 M=1 / Aquatic Chronic 1, H410 M=1
124-38-9		carbon dioxide	2,5 < 10	Press. Gas (Liq), H280

REACH

CAS No	Name	REACH registration number
67-63-0	propan-2-ol	01-2119457558-25
5989-27-5	(R)-p-mentha-1,8-diene	01-2119529223-47
124-38-9	carbon dioxide	not subject to registration

Labelling for contents according to regulation (EC) No 648/2004, annex VII

15 % or over but less than 30 % (R)-(+)-Limonene.

30 % and more aliphatic hydrocarbons

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove contaminated soaked clothing immediately.

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off with soap and water.

Consult a doctor if skin irritation persists.

In case of eye contact

In case of contact with eyes rinse thoroughly with plenty of water and seek medical advice.

In case of ingestion

Do not induce vomiting.

Medical treatment.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam

Dry powder

Carbon dioxide

Water mist

Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

Danger of bursting

In case of fire formation of dangerous gases possible.

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

Do not inhale explosion and/or combustion gases.

Additional information

Cool endangered containers with water spray jet.

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Ensure adequate ventilation.

Use personal protective clothing.

Keep away sources of ignition.

For emergency responders

Use personal protective clothing.

6.2. Environmental precautions

Inform pollution control authorities if product gets into the sewerage systems or open waters.

Do not discharge into the drains/surface waters/groundwater.

6.3. Methods and material for containment and cleaning up

Disposal according to regulations.

Take up residues with absorbent material (e.g. sand, sawdust, general-purpose binder).

6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

General protective measures

Avoid contact with eyes and skin

Do not inhale gases/vapours/aerosols.

Hygiene measures

At work do not eat, drink, smoke or take drugs.

Remove soiled or soaked clothing immediately.

Work in rooms with good ventilation.

Wash hands before breaks and after work.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking

Do not spray on a naked flame or any incandescent material.

Pressurized container.

Do not pierce or burn even after use.

Vapours can form an explosive mixture with air.

Take precautionary measures against static discharges.

Avoid effect of heat.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Adhere to administrative regulations relating to storage of compressed gas cylinders / containers.

Advice on storage compatibility

Do not store together with animal feedstuffs.

Do not store together with food.

Further information on storage conditions

Protect from heat and direct solar radiation.

Keep container dry and store at cool and aired place.

Storage temperature may not exceed 50°C (=122°F).

7.3. Specific end use(s)

Recommendation(s) for intended use

See section 1.2

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Ingredients with occupational exposure limits to be monitored

CAS No	Name	Code	[mg/m3]	[ppm]	Remark
124-38-9	Carbon dioxide	8 hours	9150	5000	EH40/2005
		Short-term	27400	15000	
67-63-0	propan-2-ol	8 hours	999	400	EH40/2005
		Short-term	1250	500	

DNEL-/PNEC-values

DNEL worker

CAS No	Substance name	Value	Code	Remark
67-63-0	propan-2-ol	888 mg/kg bw/day	DNEL long-term dermal (systemic)	
		500 mg/m ³	DNEL long-term inhalative (systemic)	

Additional advice

The statutory local and national regulations have to be observed.

8.2. Exposure controls

Respiratory protection

If ventilation insufficient, wear respiratory protection.

Short term: filter apparatus, Filter A/P2

Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves. Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: Nitrile rubber; 0,4mm; 480min; 60min.

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Eye protection

Tightly fitting goggles

Other protection measures

Protective clothing

Appropriate engineering controls

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Colour	Odour
Aerosol	Colourless, clear	Citrusfruchtartig

Odour threshold

not determined

Important health, safety and environmental information

Value	Temperature	at Method	Remark
pH value	not determined		
boiling point	82 °C		
melting point	not determined		
Flash point	not applicable		Aerosol
Vapourisation rate	not determined		
Flammable (solid)	not applicable		
Flammability (gas)	not applicable		
Ignition temperature	> 200 °C		estimate

Value	Temperature	at Method	Remark
Self ignition temperature			The product is not self-igniting.
Lower explosion limit	0,7 Vol-%		
Upper explosion limit	12 Vol-%		
Vapour pressure	43 hPa	20 °C	
Relative density	0,82 g/cm ³	20 °C	
Vapour density	not determined		
Solubility in water			No or low immiscibility
Solubility/other	not determined		
Partition coefficient noctanol/ water (log P O/W)	not determined		
Decomposition temperature	not determined		
Viscosity dynamic	not determined		
Viscosity kinematic	not determined		
Solvent content	96,7 %		
Solids content	0,8 %		

Oxidising properties

No information available.

Explosive properties

The product is considered non-explosive ; nevertheless explosive vapour/air mixtures can be generated .

9.2. Other information

No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

The product is chemically stable under recommended conditions of storage, use and temperature.

10.3. Possibility of hazardous reactions

No information available.

10.4. Conditions to avoid

Keep away from heat.

Formation of explosive gas/air mixtures.

10.5. Incompatible materials

No information available.

10.6. Hazardous decomposition products

Thermal decomposition

Remark No decomposition if used as directed.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity/Irritation/Sensitization

Value/Validation	Species	Method	Remark
LD50 acute oral	4400 mg/kg	rat	CAS: 5989-27-5
LD50 acute dermal	> 2000 mg/kg	rabbit	CAS: 5989-27-5
LC50 acute inhalation	25000 mg/m ³ (6 h)	rat	CAS: 67-63-0

inhalation

Skin irritation irritant

Eye irritation irritant

Skin sensitization sensitizing

Subacute Toxicity - Carcinogenicity

Value	Species	Method	Validation
Mutagenicity			No experimental information on genotoxicity in vitro available.
Reproduction-Toxicity			No indications of toxic effects were observed in reproduction studies in animals.
Carcinogenicity			No indications of carcinogenic effects are available from long-term trials.

Specific target organ toxicity (single exposure)

May cause drowsiness or dizziness.

Experiences made from practice

Often and long skin contact may cause degreasing and desiccation of the skin which may cause skin irritation.

Irritates respiratory tract.

Inhalation causes narcotic effect/intoxication.

Additional information

The product is to be handled with the caution usual with chemicals.

Other hazardous properties may not be excluded.

The product has not been tested. The information is derived from the properties of the individual components.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicological effects

Value	Species	Method	Validation
Fish	LC50 9640 mg/l (96 h)	Pimephales promelas	CAS: 67-63-0
Daphnia	LC50 9714 mg/l (24 h)	Daphnia magna	CAS: 67-63-0
Algae	LOEC 1000 mg/l (8 d)		CAS: 67-63-0

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

The product has not been tested. Because of the product's consistency and low solubility in water bioavailability is not likely.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects

General regulation

Toxic to aquatic life, fishes and plankton.

Even in the event of low quantities penetration into the underground drinking water is contaminated.

Product is not allowed to be discharged into aquatic environment, drains or sewage treatment plants.

The ecotoxic effect of the product has not been tested. The information on this is given on the basis of details in the literature.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste code No.

Name of waste

15 01 04

metallic packaging

15 01 10*

packaging containing residues of or contaminated by hazardous substances

Wastes marked with an asterisk are considered to be hazardous waste pursuant to Directive 2008/98/EC on hazardous waste.

Recommendations for the product

Remove in accordance with local official regulations.

There are no harmonised regulations on the disposal of chemicals in the member states of the EU. In Germany the Recycling and Waste Management Act (KrWG) stipulates recycling as a requirement.

Recommendations for packaging

Dispose of according to the local waste regulations.

Packaging that cannot be cleaned should be disposed of like the product.

General information

For proper waste disposal a complete emptying of the tin is necessary.

Assignment to a waste code number / waste identification according to the EWC is to be carried out on a sector or process-specific basis.

SECTION 14: Transport information

	ADR/RID	IMDG I	ATA-DGR
14.1. UN number	1950	1950	1950
14.2. UN proper shipping name	AEROSOLS ((R)-p mentha-1,8-diene)	AEROSOLS ((R)-p-mentha-1,8-diene)	Aerosols, flammable ((R)-p mentha-1,8-diene)
14.3. Transport hazard class(es)	2.1	2.1	2.1
14.4. Packing group	-	-	-
14.5. Environmental hazards	Yes	Yes	Yes

14.6. Special precautions for user

No information available.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

Land and inland navigation transport ADR/RID

Hazard label(s) 2.1

tunnel restriction code D

Classification code 5F

transport in "limited quantities" according to 3.4 ADR is possible

Marine transport IMDG

MARINE POLLUTANT

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC standard

VOC content 96,7 %

VOC value 792,9 g/L

15.2. Chemical Safety Assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Danish MAL Code 4-3

Indication of changes: = Data changed compared with the previous version. Previous version: 2.1

H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H280	Contains gas under pressure; may explode if heated.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.

Part Number

MP004344

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.