



Air solenoid valve

JMFH-5-1/8

Part number: 8820

FESTO



Data sheet

Feature	Value
Valve function	5/2, bistable
Lap	Underlap
Actuation type	Electrical
Width	26 mm
Standard nominal flow rate	600 l/min
Pneumatic working port	G1/8
Operating voltage	Via solenoid coil, to be ordered separately
Operating pressure	1.5 bar ... 8 bar
Design	Plate seat
Degree of protection	IP65
Certification	c UL us - Recognized (OL)
Nominal width	5 mm
Width dimension	27 mm
Type code	JMFH
Exhaust air function	With flow control option
Sealing principle	Soft
Mounting position	Any
Manual override	Detenting
Type of control	Pilot-controlled
Flow direction	Non-reversible
Symbol	00995754
Max. switching frequency	25 Hz
Changeover time	10 ms
Max. positive test pulse with 0 signal	2200 µs
Max. negative test pulse on 1 signal	3700 µs
Coil characteristics	See solenoid coil, to be ordered separately
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Storage temperature	-20 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-5 °C ... 40 °C
Product weight	260 g
Electrical connection	Via F coil, to be ordered separately

Feature	Value
Type of mounting	On terminal strip With through-hole Optionally:
Pilot exhaust air port 82	M5
Pilot exhaust air port 84	M5
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8
Pneumatic connection 3	G1/8
Pneumatic connection 4	G1/8
Pneumatic connection 5	G1/8
Note on materials	RoHS-compliant
Seals material	NBR TPE-U(PU)
Housing material	Die-cast aluminum