


Proximity sensor SME-10M-ZS-24V-E-2,5-L-OE

Part number: 551369

FESTO



Data sheet

Feature	Value
Type code	SME
Electrical connection 1, connection technology	Open end
Electrical connection 1, connection type	Cable
Electrical connection 1, number of pins/wires	2
Design	for round slot
Conforms to standard	EN 60947-5-2
Symbol	00991624
Certification	C-Tick
CE marking (see declaration of conformity)	As per EU EMC directive
Special features	Oil-resistant
Note on materials	Free of copper and PTFE Halogen-free RoHS-compliant
Measured variable	Position
Measuring principle	Magnetic reed
Ambient temperature	-40 °C ... 70 °C
Switching output	Contact-based, bipolar
Switching element function	N/O contact
Switching output repetition accuracy in ± mm	0.1 mm
On time	≤1.2 ms
Switch-off time	≤1 ms
Max. switching frequency	50 Hz
Max. output current	100 mA
Max. output current in mounting kits	50 mA
Min. switching capacity AC	3 VA
Max. switching capacity DC	9 W
Max. switching capacity DC in mounting kits	1.5 W
Max. switching capacity AC in mounting kits	1.5 VA
Voltage drop	≤4.5 V
Short-circuit protection	no
Overload protection	Not available
Rated operating voltage DC	24 V
Operating voltage range AC	5 V ... 30 V
DC operating voltage range	5 V ... 30 V
Reverse polarity protection	Bipolar
Connection outlet orientation	Longitudinal

Feature	Value
Connector cable test conditions	Test conditions on request Cable chain: 5 million cycles, bending radius 28 mm Flexural strength: as per Festo standard Torsional resistance: > 300 000 cycles, ±270°/0.1 m
Cable length	2.5 m
Cable characteristic	Suitability for energy chains/robot applications
Material of cable sheath	TPE-U(PUR)
Type of mounting	Screwed tightly Can be inserted in slot from above
Max. tightening torque	0.4 Nm
Mounting position	Any
Product weight	14.6 g
Housing material	PA-reinforced High-alloy stainless steel
Switching status indication	LED yellow
Ambient temperature with flexible cable installation	-20 °C ... 70 °C
Degree of protection	IP65 IP68