



Connecting cable NEBU-M12W5-K-2.5-LE5

Part number: 567843

FESTO



Data sheet

Feature	Value
Type code	NEBU
Conforms to standard	EN 61076-2-101
Explosion prevention and protection	Zone 22 (ATEX) Observe the information on the certificate Zone 2 (ATEX)
Cable designation	With 2x label holders
Product weight	79 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00995384
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
DC operating voltage range	0 V ... 60 V
Operating voltage range AC	0 V ... 60 V
Current rating at 40°C	4 A
Surge resistance	1.5 kV
Cable length	2.5 m
Cable characteristic	Standard
Connector cable test conditions	Test conditions on request Cable chain: 5 million cycles, bending radius 75 mm Flexural strength: as per Festo standard
Cable diameter	4.5 mm
Cable diameter tolerance	± 0.1 mm
Cable design	5 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²

Feature	Value
Degree of protection	IP65 IP69K IP68
Note on degree of protection	In mounted state
Special features	Oil-resistant
Ambient temperature	-25 °C ... 70 °C
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
Note on materials	Free of copper and PTFE RoHS-compliant Free of phosphoric acid ester Halogen-free
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PUR)
Housing colour	Black
Material of screw-type lock	Brass, nickel-plated
Insulating sheath material	PP