

CAS SMD SFTY 250, Ceramic, 270 pF, 20%, X7R, Industrial Grade, Safety MLCC, X1/Y2, 2220

**Dimensions**

<b>Chip Size</b>	2220
<b>L</b>	5.7mm +/-0.4mm
<b>W</b>	5mm +/-0.4mm
<b>T</b>	2mm +/-0.2mm
<b>S</b>	4mm MIN
<b>B</b>	0.6mm +/-0.3mm

**Packaging Specifications**

<b>Packaging:</b>	T&R
<b>Packaging Quantity:</b>	1000

**General Information**

<b>Series:</b>	CAS SMD SFTY 250
<b>Style:</b>	SMD Chip
<b>Description:</b>	Industrial Grade, Safety MLCC
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Safety Class:</b>	X1/Y2
<b>AEC-Q200:</b>	No
<b>Halogen Free:</b>	Yes

**Specifications**

<b>Capacitance:</b>	270 pF
<b>Measurement Condition:</b>	1 kHz 1Vrms
<b>Capacitance Tolerance:</b>	20%
<b>Voltage AC:</b>	250 VAC (X1), 250 VAC (Y2)
<b>Temperature Range:</b>	-55/+125°C
<b>Temperature Coefficient:</b>	X7R
<b>Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):</b>	15%, 1kHz 1.0Vrms
<b>Dissipation Factor:</b>	2.5% 1 kHz 1.0Vrms
<b>Insulation Resistance:</b>	10 GOhms