

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 5472C
Page 1 of 2 Pages

Issue: 5
Issue Date: 5/23/2005
Effective Date: 8/1/2005

A. Construction

Diameters

- | | | | |
|----|----------------|-----------------------------------|-------|
| 1) | Component 1 | 2 X 1 PAIR | |
| | a) Conductor | 24 (7/32) AWG TC | |
| | b) Insulation | 0.010" Wall, Nom. PVC, Semi Rigid | 0.044 |
| | (1) Color Code | Alpha Wire Color Code K | |
-
- | Pair | Color | Pair | Color | Pair | Color |
|------|-----------|------|-------------|------|-------|
| 1 | BLACK-RED | 2 | BLACK-WHITE | | |
-
- | | | | |
|----|-------------------|--|--------------------|
| c) | Pair | 2/Cond Cabled Together | |
| | (1) Twists: | 9.6 Twists/foot (min) | |
| 2) | Cable Assembly | 2 Components Cabled | |
| | a) Twists: | 6.0 Twists/foot (min) | |
| 3) | Shield: | Alum/Mylar Tape, 25% Overlap, Min. | |
| | a) Foil Direction | Foil Facing In | |
| | b) Drain Wire | 24 (7/32) AWG TC | |
| 4) | Jacket | 0.032" Wall, Nom.,PVC | 0.212 (0.225 Max.) |
| | a) Color(s) | GRAY | |
| | b) Print | ALPHA WIRE-* P/N 5472C 2PR 24 AWG
SHIELDED 75C (UL) TYPE CM OR AWM 2464 --- LLXXXXXX
CSA TYPE CMG FT4 ROHS | |

* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

- | | | | |
|----|--------------------------------|--|-------------|
| 1) | UL | AWM/STYLE2464 | 80°C / 300V |
| | | CM | 75°C |
| 2) | CSA International | CMG | 60°C |
| | | FT4 | |
| 3) | EU Directive 2002/95/EC(RoHS): | All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture. | |
| 4) | California Proposition 65: | The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65. | |

C. Physical & Mechanical Properties

- | | | |
|----|-------------------|--------------------|
| 1) | Temperature Range | -20 to 80°C |
| 2) | Bend Radius | 10X Cable Diameter |
| 3) | Pull Tension | 17.6 Lbs, Maximum |

D. Electrical Properties

(For Engineering purposes only)

- | | | |
|----|--------------------------|------------------------------|
| 1) | Voltage Rating | 300 V _{RMS} |
| 2) | Mutual Capacitance | 28 pf/ft @1 kHz, Nominal |
| 3) | Ground Capacitance | 50 pf/ft @1 kHz, Nominal |
| 4) | Characteristic Impedance | 64 Ω |
| 5) | Inductance | 0.19 μH/ft, Nominal |
| 6) | Conductor DCR | 26 Ω/1000ft @20°C, Nominal |
| 7) | OA Shield DCR | 15.9 Ω/1000ft @20°C, Nominal |

E. Other

- | | |
|----|------------|
| 1) | Packaging |
| | a) 1000 FT |

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 5472C
Page 2 of 2 Pages

Issue: 5
Issue Date: 5/23/2005
Effective Date: 8/1/2005

- b) 500 FT
- c) 100 FT
- d) Bulk(Made-to-order)

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.