

PRO-ELEC



Solar Torch Light Model: PEL01356

Please read these instructions carefully before use and retain for future reference.

IMPORTANT SAFETY INFORMATION

- Avoid locations of high temperature or humidity.
- The lamp is rated at IP65 for external use.

WHAT'S INCLUDED

- Lamp assembly.
- User manual.

INSTALLATION

- Installation is simply embedding the spike in the ground, ensuring the solar panel is exposed for maximum charging efficiency but not in the vicinity of other artificial light source or the low light illumination may not function.

OPERATION

- **Allow at least 8hrs for the battery to fully charge initially.**

NOTE: the lamp does not light except in low ambient light levels.

- When the ambient light falls below a preset level the LEDs will illuminate in one of three modes:

Press button once: operates in a flame effect mode.

Press button twice: operates in a fade mode.

Press button three times: the lamp illuminates constantly with no effect.

CLEANING & MAINTENANCE

- Clean the unit only with a damp cloth. Do not use any chemicals, abrasives or solvents that could damage the casing or lens.
- During periods where the lamp may not be used, it is advisable to charge the battery occasionally by exposing the solar panel to a light source to maintain it's performance and before re-using the lamp.

SPECIFICATION

Solar panel: Monocrystal 5.5V 130MA

Battery: 1 x 2200mA Lithium non-replaceable battery.

LED: 96 x warm white LED sheet.

Working time: up to 10 hours.

Dimensions: DIA120 x H780mm.



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP

Man Rev 1.1