


Pressure sensor SPAN-B2R-R18M-PN-PN-L1

Part number: 8035548

FESTO



Data sheet

Feature	Value
Type code	SPAN
Electrical connection 1, connection technology	Connection diagram L1J
Electrical connection for input 1, connection pattern	00995428
KC characters	KC EMC
Electrical connection 1, connection type	Plug
Electrical connection 1, number of pins/wires	4
Symbol	00995686
Certification	c UL us - Listed (OL) RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
Certificate issuing authority	UL E322346
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Method of measurement	Piezoresistive pressure sensor
Pressure measuring range initial value	-1 bar
Pressure measuring range end value	1 bar
Max. overload pressure	5 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible
Temperature of medium	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Accuracy in ± % FS	1.5 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature co-efficient in ± %FS/K	0.05 %FS/K
Switching output	2 x PNP or 2 x NPN switchable
Switching function	Threshold value comparator Auto difference monitoring Window comparator
Switching element function	N/C contact/N/O contact switchable
Max. output current	100 mA
Short-circuit protection	yes
DC operating voltage range	15 V ... 30 V
Reverse polarity protection	for all electrical connections
Electrical connection	4-pin Plug Rectangular design

Feature	Value
Type of mounting	With wall/surface bracket With thread Front panel mounting
Mounting position	Any
Pneumatic connection	External thread R1/8 Internal thread M5
Product weight	46 g
Housing material	PA-reinforced
Display type	Illuminated LCD
Displayable unit(s)	kgf/cm ² inchHg inchH2O mmHg kPa bar psi MPa
Setting options	Teach-in Via display and pushbuttons
Protection against tampering	PIN code
Threshold value setting range	0 % ... 100 %
Hysteresis setting range	0 % ... 90 %
Degree of protection	IP40
Corrosion resistance class (CRC)	2 - Moderate corrosion stress