

Product availability : Non-Stock - Not normally stocked in distribution facility



## Main

Range	TeSys
Device short name	LUL
Product or component type	Communication module
Product compatibility	LUCB LUCM LUCC LUCL LUCD LUCA
Device application	Communication
Range compatibility	TeSys U LUB non reversing power base TeSys U LU2B reversing power base

## Complementary

Main function available	Communication module
Mounting mode	Plug-in
Mounting location	Front side
Physical interface	9-way SUB-D male
Bus type	Profibus DP
Communication port protocol	Profibus DP
Addressing	1...125
Current consumption	1.5 mA 24 V DC 20...28 V
Logic input	Positive 24 V DC - 7 mA
Response time	10 ms +/- 30 % change to state 0 10 ms +/- 30 % change to state 1
Input type	Resistive
Number of outputs	2 dedicated to starter-controller coil operation 1

[Us] rated supply voltage	24 V DC
Output current	<= 500 mA
Protection type	GL fuse 2 A
Switching current capacity	0.5 mA 24 V
Local signalling	3 LEDs front panel

## Environment

Standards	Profibus DP
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
IP degree of protection	IP20 IEC 60529

## Ordering and shipping details

Category	22398 - TESYS U - MULTI-FCTN CTRL MOD(LUCM)
Discount Schedule	I11
GTIN	00785901556275
Returnability	No
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------