



Main

Range of product	TeSys
Device short name	GS2AF
Product or component type	Auxiliary contact
Contact application	Blown fuse signalling
Contacts type and composition	1 C/O
Contact operation	Instantaneous
[I _{th}] conventional free air thermal current	16 A (at 40 °C)
[I _e] rated operational current	12 A at 24 V DC-13 2 A at 48 V DC-13 3 A at 400 V AC-15 4 A at 230 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13

Complementary

Range compatibility	TeSys GS fuse-switch disconnectors
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-15
Product compatibility	GS
Poles description	3P
Switch rated current	630 A
Fuse type	DIN NFC
Fuse size	3
Net weight	0.46 kg

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------