

**Symphony**

# EVAPORATIVE COOLERS SILVER E



**1 YEAR WARRANTY**

Powered by



consumes 68 watts only



also works on inverter power



use it outside, use it inside



delivers fresh, filtered cool air



**Dura-Pump Technology**  
For Long Life Of The Pump



**Intelligent Remote**  
Full Function Remote With Timer



**Feather-Touch Digital Control Panel**  
For Ease Of Operation



**System Restore Function**  
Remembers & Restores Previous Settings



**Powerful Air Throw With Auto Swing**  
For Faster Cooling



**Cool Flow Dispenser**  
Channelised Water Distribution For Superior Cooling



**Large Tank Capacity**  
Gives Uninterrupted Night-Long Cooling



**Whisper-quiet Performance**  
For sound sleep



**High Efficiency Cooling Pads**  
For Enhanced Cooling

Cat No.	Silver E
Cooling Area (approx.) sqm	23
Air Throw dist (approx.) mtr/ft	6/20
Blower/fan dia (mm)	120
Speed Control	5
Motor R.P.M.	1400
Air delivery m3/hr / CFM	1100/647
Electrical - 230V / 50Hz (W)	68
Water tank capacity (Ltrs)	9
Water inlet - Back	Yes
Mosquito net / Dust filter	Yes
Auto Shut-off Pump	Yes
Ice Chamber	Yes
Cooling media	Honeycomb
Remote Control (requires CR2032 cell)	Yes
Noise dB (A) 1m Low-High	44-59
Length (mm)	295
Width (mm)	318
Height (mm)	692
Net Weight (Kgs)	7