



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or component type	Enclosure
Material	Polycarbonate
Device composition	Contacteur ordered separately Thermal overload relay ordered separately
Product compatibility	LE1D18...35
Control type	Push-button reset blue R

Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 16 bottom 2 ISO25 top 2 Pg 21 bottom 2 ISO25 bottom
Height	201 mm
Width	103 mm
Depth	154 mm
Net weight	0.5 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------