



Main

Range	TeSys
Product name	TeSys Integral 63
Product or component type	Contactor breaker
Device short name	LD1LD

Complementary

Utilisation category	AC-43
Poles description	3P
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ie] rated operational current	63 A AC AC-43
[Ith] conventional free air thermal current	63 A (at 40 °C)
Motor power kW	15 kW at 220...240 V AC 50/60 Hz 30 kW at 400 V AC 50/60 Hz 33 kW at 415 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz 55 kW at 660 V AC 50/60 Hz 33 kW at 440 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Control type	Knob black front
Irms rated making capacity	756 A conforming to IEC 60947-4 946 A conforming to IEC 60947-4
[Ipk] rated peak withstand current	105 kA conforming to IEC 60947-2
Breaking capacity	Icu 10 kA at 600...690 V (cos φ 0.5) conforming to IEC 60947-2 Icu 30 kA at 480...525 V (cos φ 0.25) conforming to IEC 60947-2 Icu 50 kA at ≤ 440 V (cos φ 0.25) conforming to IEC 60947-2
[Ics] rated service breaking capacity	10 kA at 600...690 V conforming to IEC 60947-2 35 kA at 480...525 V conforming to IEC 60947-2 50 kA at ≤ 440 V conforming to IEC 60947-2
Maximum breaking time	4 ms
Thermal stress limit	300000 A ² .s
[Uimp] rated impulse withstand voltage	8 kV IEC 60947-4
Control circuit voltage limits	0.25...0.7 Uc drop-out 55 °C 0.85...1.1 Uc operation 55 °C
[Ui] rated insulation voltage	690 V conforming to IEC 60947-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Inrush power in W	300 W (at 20 °C)
Hold-in power consumption in W	8 W at 20 °C
Heat dissipation	5 W at 32 A per pole, hot state for power circuit 7 W at 50 A per pole, hot state for power circuit 9 W at 63 A per pole, hot state for power circuit 4.4 W at 25 A per pole, hot state for power circuit 5.8 W at 40 A per pole, hot state for power circuit
Operating time	15...25 ms DC network opening at 20 °C for control circuit 25...40 ms DC network closing at 20 °C for control circuit
Electrical durability	1 Mcycles on AC-3 3 kA at 415 V - after 1 cycle O-CO-r-CO at Isc 0.9 Mcycles on AC-3 10 kA at 415 V - after 1 cycle O-CO-r-CO at Isc 0.6 Mcycles on AC-3 25 kA at 415 V - after 1 cycle O-CO-r-CO at Isc 0.5 Mcycles on AC-3 35 kA at 415 V - after 1 cycle O-CO-r-CO at Isc 0.2 Mcycles on AC-3 50 kA at 415 V - after 1 cycle O-CO-r-CO at Isc
Mechanical durability	1.2 Mcycles
Connections - terminals	Power circuit: screw clamp terminals 1 cable(s) 6...50 mm ² - flexible - without cable end Power circuit: screw clamp terminals 2 cable(s) 6...25 mm ² - flexible - without cable end Power circuit: screw clamp terminals 1 cable(s) 6...25 mm ² - flexible - with cable end Power circuit: screw clamp terminals 2 cable(s) 6...25 mm ² - flexible - with cable end Power circuit: screw clamp terminals 1 cable(s) 6...50 mm ² - solid
Tightening torque	Power circuit: 6 N.m - on screw clamp terminals
Width	90 mm
Height	243 mm
Depth	192 mm
Net weight	3.7 kg

Environment

Standards	VDE 0110 NBN IEC 60158-1 NF C 63-650 IEC 60204-1 IEC 60947-2 IEC 60947-1 VDE 0171 BS 4941 VDE 0170 VDE 471 NF C 63-120 IEC 60204-2 NF C 63-130 IEC 60947-4 BS 4752 NF C 79-100 VDE 0660 VDE 0100 BS 5424 NF C 63-110 NF C 20-040 NEN IEC 60364 VDE 0113
Product certifications	ASEFA LROS (Lloyds register of shipping) RINA DEMKO UL SETI SCC CSA NKK DNV NEMKO ASTA ASE OVE BV GL USSR

Protective treatment	TH
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C
Mechanical robustness	Vibrations de-energised: 3 Gn, 1...300 Hz Vibrations energised: 3 Gn, 1...300 Hz Shocks de-energised: 8 Gn for 11 ms Shocks energised: 8 Gn for 11 ms
IP degree of protection	IP20 B conforming to IEC 60144 IP20 B conforming to IEC 60529
Operating altitude	3000 m without derating

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------