



Main

Range	TeSys
Product or component type	Shunt trip
Device short name	GV7AS
Device application	Control
Range compatibility	TeSys GV5 TeSys GV6 TeSys GV7

Complementary

[Uc] control circuit voltage	110...130 V AC 50/60 Hz
Control circuit voltage limits	0.7...1.1 Un
[Ui] rated insulation voltage	690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 508 600 V AC conforming to CSA C22.2 No 14
Threshold tripping voltage	0.2...0.75 Ue
Inrush power in VA	10 VA AC
Hold-in power consumption in VA	5 VA AC
Operating time	< 50 ms conforming to IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 cable(s) 1 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 1.5 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 1.5 mm ² solid
Tightening torque	1.2 N.m on screw clamp terminals
Net weight	0.105 kg
Quantity per set	Set of 10

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
