



Commercial status

Discontinued: 01 January 2008

Main

Range	TeSys
Product or component type	Mechanical latch block
Product compatibility	LP1D40...D65 LC1D40...D65
[Uc] control circuit voltage	220/240 V AC 50/60 Hz 220/240 V DC

Complementary

Mounting location	Front side
Tripping control	Electrical Manual
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1
Power required in VA	25 for AC circuit
Power required in W	30 W for DC circuit
Mechanical durability	500000 cycles
Maximum operating rate	1200 cyc/h
On-load factor	10 %
Net weight	0.07 kg

Environment

Product certifications	CSA UL
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

LA6DK10M is replaced by:



Add-on blocks LAD6K10M

CONTACTOR MECH. LATCH CONTACT BLOCK IEC

Qty 1

Reason for substitution: End of life | Substitution date: 30 December 2007