


GS1ANT22

Auxiliary contacts, TeSys GS, 2NC + 2NO, instantaneous, left side mounting, for GS2 with front handle test position



Main

Range of product	TeSys
Device short name	GS1AN
Product or component type	Auxiliary contact
Contact application	O, I and test position signalling
Contacts type and composition	2 NO + 2 NC
Contact operation	Instantaneous
[I _{th}] conventional free air thermal current	20 A (at 40 °C)
[I _e] rated operational current	1 A at 220 V DC-13 10 A at 230 V AC-15 12 A at 127 V AC-15 4 A at 48 V DC-13 6 A at 440 V AC-15 8 A at 400/415 V AC-15 1.2 A at 110 V DC-13

Complementary

Range compatibility	TeSys GS fuse-switch disconnecter
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-15
Switch rated current	50 A 63 A 125 A 315 A 100 A 250 A 60 A 200 A 160 A 400 A
Fuse type	DIN BS NFC
Type of operating handle	External frontal
Net weight	0.258 kg

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Contractual warranty

Warranty	18 months
----------	-----------