

PRODUCT-DETAILS

# SAMHL20/25M

## 20MM GALV CORE ANTI MICRO COND 25M



### General Information

Extended Product Type	SAMHL20/25M
Product ID	7TCA296030R0440
EAN	5020963801495
Catalog Description	20MM GALV CORE ANTI MICRO COND 25M
Long Description	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 20 Millimeters / US Trade Size 1/2 Inch, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, IP40-IP69 Rating, Galvanised Steel Core, String Packed and Thermoplastic Jacket, Reel Length 25 Meters, White

### Ordering

EAN	5020963801495
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	22.37 lb 10.145 kg
--------------------	-----------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

### Additional Information

Application	Suitable for indoor splash zone areas or food processing equipment
Brand / Label	Adaptaflex
Color	White
Flexibility	High
Inside Diameter	15.9 mm
Material	Galvanised Steel Core, String Packed and Thermoplastic Jacket
Nominal Size	20 mm
Number of Batteries	0
Outside Diameter	21.1 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Anti-Microbial Conduit
Radius	80 mm
UPC	786210212951

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SAMHL20/25M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SAMHL20/25M

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

