



## Main

Range of product	TeSys
Device short name	GV2DP
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 2
Poles description	3P
Utilisation category	AC-3
Motor power kW	1.5 kW at 440 V AC 50/60 Hz 1.5 kW at 500 V AC 50/60 Hz 2.2 kW at 500 V AC 50/60 Hz 1.1 kW at 400/415 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Magnetic tripping current	51 A

## Complementary

Device composition	1 3-pole contactor 1 motor circuit breaker type GV2P 1 combination block GV2AF3
Thermal protection adjustment range	2.5...4 A
Rated breaking capacity	Iq 130 kA at 400/415 V conforming to IEC 60947-4-1 Iq 130 kA at 440 V conforming to IEC 60947-4-1 Iq 130 kA at 500 V conforming to IEC 60947-4-1
Net weight	0.696 kg
Height	176.4 mm
Width	45 mm
Depth	105.6 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------