


Connecting cable SIM-M12-4WD-5-PU

Part number: 164258

FESTO



Data sheet

Feature	Value
Type code	SIM
Conforms to standard	EN 61984 EN 61076-2-101
Electrical connection	5-pin/4-wire Angled socket/open end M12x1 / -
DC operating voltage range	0 V ... 250 V
Operating voltage range AC	0 V ... 250 V
Current rating at 40°C	4 A
Surge resistance	2.5 kV
Cable length	5 m
Cable characteristic	Standard
Connector cable test conditions	Test conditions on request Flexural strength: as per Festo standard Cable chain: 5 million cycles, bending radius 75 mm
Cable diameter	4.5 mm
Cable design	4 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²
Wire insulation color code	Blue Black White Brown
Degree of protection	IP65 IP68
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PU)
Color cable sheath	Gray
Housing material	TPE-U(PU)
Housing colour	Black

Feature	Value
Material of union nut	Nickel-plated Brass
Insulating sheath material	PP
Symbol	00991861
Plug coding	A