Note: This datasheet may be out of date  ${\color{blue} \textbf{Please download the latest datasheet of LQH2HPZ150MGR\# from the official website of Murata Manufacturing} \\$ Co., Ltd.

## LQH2HPZ150MGR#

"#" indicates a package specification code.

Size Code 2520 (1008) in mm (in inch), 1.0mm max. Thickness, Low DC resistance design



















< List of part numbers with package codes > LQH2HPZ150MGRL



## Appearance & Shape





(in mm)



When rated current is applied to the products, inductance will be within ±30% of initial inductance value range. Keep the temperature (ambient temperature plus self-generation of heat) under 125°C. When rated current is applied to the products, the self-temperature rise shall be limited to 40°C max. (ambient temperature 85°C). When rated current is applied to the products, the self-temperature rise shall be limited to 20°C max. (ambient temperature 85 °C to 105°C).

1 of 5

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





 $Please \ download \ the \ latest \ data sheet \ of \ LQH2HPZ150MGR\# from \ the \ official \ website \ of \ Murata \ Manufacturing$ Co., Ltd.

# LQH2HPZ150MGR#

"#" indicates a package specification code.



Packaging	Specifications	Minimum Order Quantity
L	180Embossed Tape	3000

Mass (typ.)	
1 piece	0.019g

2 of 5

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date.  $Please \ download \ the \ latest \ data sheet \ of \ LQH2HPZ150MGR\# from \ the \ official \ website \ of \ Murata \ Manufacturing$ Co., Ltd.

# LQH2HPZ150MGR#

"#" indicates a package specification code.



L size	2.5±0.2mm
W size	2.0±0.2mm
T size	0.9±0.1mm
Size code inch (mm)	1008 (2520)
Inductance	15µH±20%
Inductance Test Frequency	1MHz
Rated current (Isat) (Based on Inductance change)	570mA
Rated current (Itemp) (Based on Temperature rise)	560mA(Ambient temp.85°C)310mA(Ambient temp.105°C)
Max. of DC resistance	1.11Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Class of magnetic shield	Magnetic Resin
Self resonance frequency (min.)	20MHz
Operating Temperature Range(Self- temperature rise is not included)	-40°C to 105°C
DC Resistance Intermediate Values	0.925Ω±20%
Series	LQH2HPZ_GR

3 of 5

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# LQH2HPZ150MGR#

"#" indicates a package specification code.





The charts below may show another part number which shares its characteristics.











LQH2HPZ150MGR L-Current 20degC

4 of 5

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering






Note: This datasheet may be out of date Please download the latest datasheet of LQH2HPZ150MGR# from the official website of Murata Manufacturing Co., Ltd.

# LQH2HPZ150MGR#

"#" indicates a package specification code.



LQH2HPZ150MGR Temp. rise

5 of 5

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

