

**74LCX74****Low Voltage Dual D-Type Positive Edge-Triggered Flip-Flop with 5V Tolerant Inputs****General Description**

The LCX74 is a dual D-type flip-flop with Asynchronous Clear and Set inputs and complementary ( $Q$ ,  $\bar{Q}$ ) outputs. Information at the input is transferred to the outputs on the positive edge of the clock pulse. After the Clock Pulse input threshold voltage has been passed, the Data input is locked out and information present will not be transferred to the outputs until the next rising edge of the Clock Pulse input.

## Asynchronous Inputs:

- LOW input to  $\bar{S}_D$  (Set) sets  $Q$  to HIGH level
- LOW input to  $\bar{C}_D$  (Clear) sets  $Q$  to LOW level
- Clear and Set are independent of clock
- Simultaneous LOW on  $\bar{C}_D$  and  $\bar{S}_D$  makes both  $Q$  and  $\bar{Q}$  HIGH


**Features**

- 5V tolerant inputs
- 7.0 ns  $t_{PD}$  max, 10  $\mu\text{A}$   $I_{CCQ}$  max
- Power down high impedance inputs and outputs
- Supports live insertion/withdrawal
- 2.0V-3.6V  $V_{CC}$  supply operation
- $\pm 24$  mA output drive
- Implements patented noise/EMI reduction circuitry
- Functionally compatible with 74 series 74
- Latch-up performance exceeds 500 mA
- ESD performance:
  - Human body model > 2000V
  - Machine model > 200V

**Ordering Code:**




Order Number	Package Number	Package Description
74LCX74M	M14A	16-Lead (0.150" Wide) Molded Small Outline Package, SOIC, JEDEC
74LCX74SJ	M14D	14-Lead Small Outline Package, SOIC, EIAJ
74LCX74MTC	MTC14	14-Lead Thin Shrink Small Outline Package, TSSOP

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

**Connection Diagram**Pin Assignment  
for SOIC and TSSOP

DS012414-4

## Logic Symbol



## Pin Descriptions

Pin Names	Description
D <sub>1</sub> , D <sub>2</sub>	Data Inputs
CP <sub>1</sub> , CP <sub>2</sub>	Clock Pulse Inputs
̄C <sub>D1</sub> , ̄C <sub>D2</sub>	Direct Clear Inputs
̄S <sub>D1</sub> , ̄S <sub>D2</sub>	Direct Set Inputs
Q <sub>1</sub> , ̄Q <sub>1</sub> , Q <sub>2</sub> , ̄Q <sub>2</sub>	Outputs

## Truth Table

(Each Half)

Inputs				Outputs	
̄S <sub>D</sub>	̄C <sub>D</sub>	CP	D	Q	̄Q
L	H	X	X	H	L
H	L	X	X	L	H
L	L	X	X	H	H
H	H	✓	H	H	L
H	H	✓	L	L	H
H	H	L	X	Q <sub>0</sub>	̄Q <sub>0</sub>

H = HIGH Voltage Level

L = LOW Voltage Level

X = Immaterial

✓ = LOW-to-HIGH Clock Transition

Q<sub>0</sub>(̄Q<sub>0</sub>) = Previous Q(̄Q) before LOW-to-HIGH Transition of Clock

## Absolute Maximum Ratings (Note 1)

Symbol	Parameter	Value	Conditions	Units
$V_{CC}$	Supply Voltage	-0.5 to +7.0		V
$V_I$	DC Input Voltage	-0.5 to +7.0		V
$V_O$	DC Output Voltage	-0.5 to $V_{CC} + 0.5$	Output in High or Low State (Note 2)	V
$I_{IK}$	DC Input Diode Current	-50	$V_I < GND$	mA
$I_{OK}$	DC Output Diode Current	-50 +50	$V_O < GND$ $V_O > V_{CC}$	mA
$I_O$	DC Output Source/Sink Current	$\pm 50$		mA
$I_{CC}$	DC Supply Current per Supply Pin	$\pm 100$		mA
$I_{GND}$	DC Ground Current per Ground Pin	$\pm 100$		mA
$T_{STG}$	Storage Temperature	-65 to +150		°C

## Recommended Operating Conditions (Note 3)

Symbol	Parameter	Min	Max	Units
$V_{CC}$	Supply Voltage	Operating	2.0	V
		Data Retention	1.5	3.6
$V_I$	Input Voltage	0	5.5	V
$V_O$	Output Voltage	HIGH or LOW State	0	$V_{CC}$
$I_{OH}/I_{OL}$	Output Current	$V_{CC} = 3.0V - 3.6V$	$\pm 24$	mA
		$V_{CC} = 2.7V$	$\pm 12$	
$T_A$	Free-Air Operating Temperature	-40	85	°C
$\Delta t/\Delta V$	Input Edge Rate, $V_{IN} = 0.8V - 2.0V$ , $V_{CC} = 3.0V$	0	10	ns/V

**Note 1:** The Absolute Maximum Ratings are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the Absolute Maximum Ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

**Note 2:**  $I_O$  Absolute Maximum Rating must be observed.

**Note 3:** Unused inputs must be held HIGH or LOW. They may not float.

## DC Electrical Characteristics

Symbol	Parameter	Conditions	$V_{CC}$ (V)	$T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$		Units
				Min	Max	
$V_{IH}$	HIGH Level Input Voltage		2.7–3.6	2.0		V
$V_{IL}$	LOW Level Input Voltage		2.7–3.6		0.8	V
$V_{OH}$	HIGH Level Output Voltage	$I_{OH} = -100 \mu\text{A}$	2.7–3.6	$V_{CC} - 0.2$		V
		$I_{OH} = -12 \text{ mA}$	2.7	2.2		V
		$I_{OH} = -18 \text{ mA}$	3.0	2.4		V
		$I_{OH} = -24 \text{ mA}$	3.0	2.2		V
$V_{OL}$	LOW Level Output Voltage	$I_{OL} = 100 \mu\text{A}$	2.7–3.6		0.2	V
		$I_{OL} = 12 \text{ mA}$	2.7		0.4	V
		$I_{OL} = 16 \text{ mA}$	3.0		0.4	V
		$I_{OL} = 24 \text{ mA}$	3.0		0.55	V
$I_I$	Input Leakage Current	$0 \leq V_I \leq 5.5\text{V}$	2.7–3.6		$\pm 5.0$	$\mu\text{A}$
$I_{OFF}$	Power-Off Leakage Current	$V_I$ or $V_O = 5.5\text{V}$	0		10	$\mu\text{A}$
$I_{CC}$	Quiescent Supply Current	$V_I = V_{CC}$ or GND	2.7–3.6		10	$\mu\text{A}$
		$3.6\text{V} \leq V_I \leq 5.5\text{V}$	2.7–3.6		$\pm 10$	$\mu\text{A}$
$\Delta I_{CC}$	Increase in $I_{CC}$ per Input	$V_{IH} = V_{CC} - 0.6\text{V}$	2.7–3.6		500	$\mu\text{A}$

## AC Electrical Characteristics

Symbol	Parameter	$T_A = -40^\circ\text{C to } +85^\circ\text{C}, C_L = 50\text{pF}, R_L = 500\Omega$				Units	
		V <sub>CC</sub> = 3.3V ±0.3V		V <sub>CC</sub> = 2.7V			
		Min	Max	Min	Max		
f <sub>MAX</sub>	Maximum Clock Frequency	150		150		MHz	
t <sub>PHL</sub>	Propagation Delay CP <sub>n</sub> to Q <sub>n</sub> or $\bar{Q}_n$	1.5	7.0	1.5	8.0	ns	
t <sub>PLH</sub>	Propagation Delay $\bar{C}_{Dn}$ or $\bar{S}_{Dn}$ to Q <sub>n</sub> or $\bar{Q}_n$	1.5	7.0	1.5	8.0	ns	
t <sub>S</sub>	Setup Time	2.5		2.5		ns	
t <sub>H</sub>	Hold Time	1.5		1.5		ns	
t <sub>W</sub>	Pulse Width CP	3.3		3.3		ns	
t <sub>W</sub>	Pulse Width and $\bar{C}_D, \bar{S}_D$	3.3		3.6		ns	
t <sub>rem</sub>	Removal Time	2.5		3.0		ns	
t <sub>OSHL</sub>	Output to Output Skew (Note 4)		1.0			ns	
t <sub>OSLH</sub>			1.0				

**Note 4:** Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH to LOW (t<sub>OSHL</sub>) or LOW to HIGH (t<sub>OSLH</sub>).



## Dynamic Switching Characteristics

Symbol	Parameter	Conditions	V <sub>CC</sub> (V)	$T_A = 25^\circ\text{C}$	Unit
				Typical	
V <sub>OLP</sub>	Quiet Output Dynamic Peak V <sub>OL</sub>	C <sub>L</sub> = 50 pF, V <sub>IH</sub> = 3.3V, V <sub>IL</sub> = 0V	3.3	0.8	V
V <sub>OLV</sub>	Quiet Output Dynamic Valley V <sub>OL</sub>	C <sub>L</sub> = 50 pF, V <sub>IH</sub> = 3.3V, V <sub>IL</sub> = 0V	3.3	-0.8	V



## Capacitance

Symbol	Parameter	Conditions	Typical	Units
C <sub>IN</sub>	Input Capacitance	V <sub>CC</sub> = Open, V <sub>I</sub> = 0V or V <sub>CC</sub>	7	pF
C <sub>OUT</sub>	Output Capacitance	V <sub>CC</sub> = 3.3V, V <sub>I</sub> = 0V or V <sub>CC</sub>	8	pF
C <sub>PD</sub>	Power Dissipation Capacitance	V <sub>CC</sub> = 3.3V, V <sub>I</sub> = 0V or V <sub>CC</sub> , f = 10 MHz	25	pF

**Physical Dimensions** inches (millimeters) unless otherwise noted




16-Lead (0.0150" Wide) Molded Small Outline Package JEDEC  
Package Number M14A



14-Lead Small Outline Package EIAJ (SJ)  
Package Number M14D

## 74LCX74 Low Voltage Dual D-Type Positive Edge-Triggered Flip-Flop with 5V Tolerant Inputs

### Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



MTC14 (REV C)

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Fairchild Semiconductor  
Corporation  
Americas  
Customer Response Center  
Tel: 1-888-522-5372

[www.fairchildsemi.com](http://www.fairchildsemi.com)

Fairchild Semiconductor  
Europe  
Fax: +49 (0) 1 80-530 85 86  
Email: europe.support@nsc.com  
Deutsch Tel: +49 (0) 8 141-35-0  
English Tel: +44 (0) 1 793-85-68-56  
Italy Tel: +39 (0) 2 57 5631

Fairchild Semiconductor  
Hong Kong Ltd.  
13th Floor, Straight Block,  
Ocean Centre, 5 Canton Rd.  
Tsimshatsui, Kowloon  
Hong Kong  
Tel: +852 2737-7200  
Fax: +852 2314-0061

National Semiconductor  
Japan Ltd.  
Tel: 81-3-5620-6175  
Fax: 81-3-5620-6179